

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786612

Luminaire Tested: LERS6D15D010-EC6DR1515309030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D15D010-EC6DR1515309030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1484.7 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P786612
CATALOG NUMBER: LERS6D15D010-EC6DR1515309030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P786612

CATALOG NUMBER: LERS6D15D010-EC6DR1515309030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2276144	2276144	2276144
5°	1337568	1320251	1330698
10°	399207	401997	408155
15°	99295	101232	98105
20°	29710	34406	30340
25°	10470	13344	10610
30°	3849	5069	3909
35°	1924	2179	1866
40°	1214	1335	1214
45°	896	959	896
50°	716	716	716
55°	599	599	599
60°	484	484	484
65°	364	364	364
70°	314	314	314
75°	197	197	257
80°	134	134	134
85°	75	75	75

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 959 cd/sqm



TEST NUMBER: P786612

CATALOG NUMBER: LERS6D15D010-EC6DR1515309030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	962.9	64.9
10°-20°	396.1	26.7
20°-30°	78.7	5.3
30°-40°	19.6	1.3
40°-50°	10.3	0.7
50°-60°	7.7	0.5
60°-70°	5.4	0.4
70°-80°	3.1	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1437.7	96.8
0°-40°	1457.3	98.2
0°-60°	1475.3	99.4
0°-90°	1484.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1484.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	20229	20229	20229	20229	20229	
5°	13161	13026	12991	13081	13094	961
15°	1143	1165	1166	1145	1130	392
25°	134	152	171	152	136	71
35°	26	28	30	28	26	18
45°	13	13	14	13	13	10
55°	9	9	9	9	9	8
65°	5	5	5	5	5	5
75°	3	3	3	3	3	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P786612

CATALOG NUMBER: LERS6D15D010-EC6DR1515309030-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	20228.8	20228.8	20228.8	20228.8	20228.8
2.5°	18247.2	18262.7	18268.6	18286.6	18353.4
5°	13161.3	13026.0	12990.9	13080.8	13093.7
7.5°	7796.3	7823.7	7923.9	7946.1	7865.6
10°	4278.4	4313.5	4308.3	4339.2	4374.3
12.5°	2188.0	2160.6	2152.0	2187.1	2138.3
15°	1143.2	1164.6	1165.5	1144.9	1129.5
17.5°	614.9	639.7	680.8	647.4	596.0
20°	363.1	385.4	420.5	393.1	370.8
22.5°	224.4	242.3	267.2	245.8	227.8
25°	134.4	152.4	171.3	151.6	136.2
27.5°	79.6	95.1	107.0	94.2	78.8
30°	51.4	59.9	67.7	59.1	52.2
32.5°	36.0	39.4	42.8	39.4	36.0
35°	26.5	28.3	30.0	28.3	25.7
37.5°	20.6	22.3	23.1	21.4	19.7
40°	17.1	18.0	18.8	18.0	17.1
42.5°	14.6	15.4	15.4	15.4	14.6
45°	12.8	12.8	13.7	12.8	12.8
47.5°	11.1	11.1	12.0	11.1	11.1
50°	10.3	10.3	10.3	10.3	10.3
52.5°	9.4	9.4	9.4	9.4	9.4
55°	8.6	8.6	8.6	8.6	8.6
57.5°	7.7	7.7	7.7	7.7	7.7
60°	6.9	6.9	6.9	6.9	6.9
62.5°	6.0	6.0	6.0	6.0	6.0
65°	5.1	5.1	5.1	5.1	5.1
67.5°	5.1	5.1	5.1	5.1	5.1
70°	4.3	4.3	4.3	4.3	4.3
72.5°	3.4	3.4	3.4	3.4	3.4
75°	2.6	2.6	2.6	2.6	3.4
77.5°	2.6	2.6	2.6	2.6	2.6
80°	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7
85°	0.9	0.9	0.9	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)