

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786665

Luminaire Tested: LERS6D15D010-EC6DR250215IC9040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D15D010-EC6DR250215IC9040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2487.1 lumens
Efficiency: N/A
Efficacy: 157.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786665

CATALOG NUMBER: LERS6D15D010-EC6DR250215IC9040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P786665

CATALOG NUMBER: LERS6D15D010-EC6DR250215IC9040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89			89
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85			85
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82			82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			79
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77			77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			74
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72			72
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69			69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1030668
5°	959936
10°	684749
15°	403289
20°	250940
25°	137711
30°	62981
35°	23849
40°	10797
45°	6490
50°	2703
55°	1733
60°	1224
65°	827
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6490 cd/sqm



TEST NUMBER: P786665

CATALOG NUMBER: LERS6D15D010-EC6DR250215IC9040-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	752.2	30.2
10°-20°	1018.8	41.0
20°-30°	539.1	21.7
30°-40°	133.1	5.4
40°-50°	32.5	1.3
50°-60°	8.5	0.3
60°-70°	2.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2310.1	92.9
0°-40°	2443.2	98.2
0°-60°	2484.2	99.9
0°-90°	2487.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2487.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9433	
5°	8752	752
15°	3565	1019
25°	1142	539
35°	179	133
45°	42	32
55°	9	9
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786665

CATALOG NUMBER: LERS6D15D010-EC6DR250215IC9040-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	9433.1
2.5°	9278.1
5°	8752.3
7.5°	7696.1
10°	6171.9
12.5°	4665.6
15°	3565.3
17.5°	2778.7
20°	2158.2
22.5°	1618.5
25°	1142.3
27.5°	766.0
30°	499.2
32.5°	303.7
35°	178.8
37.5°	109.4
40°	75.7
42.5°	57.9
45°	42.0
47.5°	25.4
50°	15.9
52.5°	11.5
55°	9.1
57.5°	7.1
60°	5.6
62.5°	4.4
65°	3.2
67.5°	1.2
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)