

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785361

Luminaire Tested: LERS6D02D010-EC6DR150210IC9027-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P785361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D02D010-EC6DR150210IC9027-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 373.2 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785361

CATALOG NUMBER: LERS6D02D010-EC6DR150210IC9027-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P785361

CATALOG NUMBER: LERS6D02D010-EC6DR150210IC9027-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	92						92													
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	92	90						90													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	89						89													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	88						88													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	87						87													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	86						86													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	84						84													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	572096	572096	572096
5°	336188	331839	334461
10°	100334	101043	102592
15°	24954	25440	24659
20°	7470	8649	7626
25°	2633	3350	2664
30°	966	1273	981
35°	487	545	472
40°	305	334	305
45°	224	238	224
50°	181	181	181
55°	153	153	153
60°	119	119	119
65°	93	93	93
70°	80	80	80
75°	45	45	68
80°	32	32	32
85°	17	17	17

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 238 cd/sqm



TEST NUMBER: P785361

CATALOG NUMBER: LERS6D02D010-EC6DR150210IC9027-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.0	64.9
10°-20°	99.6	26.7
20°-30°	19.8	5.3
30°-40°	4.9	1.3
40°-50°	2.6	0.7
50°-60°	1.9	0.5
60°-70°	1.4	0.4
70°-80°	0.8	0.2
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	361.4	96.8
0°-40°	366.3	98.2
0°-60°	370.8	99.4
0°-90°	373.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	373.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5084	5084	5084	5084	5084	
5°	3308	3274	3265	3288	3291	242
15°	287	293	293	288	284	99
25°	34	38	43	38	34	18
35°	7	7	8	7	6	5
45°	3	3	3	3	3	3
55°	2	2	2	2	2	2
65°	1	1	1	1	1	1
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P785361

CATALOG NUMBER: LERS6D02D010-EC6DR150210IC9027-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5084.4	5084.4	5084.4	5084.4	5084.4
2.5°	4586.4	4590.2	4591.7	4596.3	4613.1
5°	3308.0	3274.0	3265.2	3287.8	3291.0
7.5°	1959.6	1966.4	1991.6	1997.2	1977.0
10°	1075.3	1084.2	1082.9	1090.6	1099.5
12.5°	549.9	543.1	540.9	549.7	537.5
15°	287.3	292.7	292.9	287.8	283.9
17.5°	154.5	160.8	171.1	162.7	149.8
20°	91.3	96.9	105.7	98.8	93.2
22.5°	56.4	60.9	67.2	61.8	57.3
25°	33.8	38.3	43.0	38.1	34.2
27.5°	20.0	23.9	26.9	23.7	19.8
30°	12.9	15.1	17.0	14.9	13.1
32.5°	9.0	9.9	10.8	9.9	9.0
35°	6.7	7.1	7.5	7.1	6.5
37.5°	5.2	5.6	5.8	5.4	5.0
40°	4.3	4.5	4.7	4.5	4.3
42.5°	3.7	3.9	3.9	3.9	3.7
45°	3.2	3.2	3.4	3.2	3.2
47.5°	2.8	2.8	3.0	2.8	2.8
50°	2.6	2.6	2.6	2.6	2.6
52.5°	2.4	2.4	2.4	2.4	2.4
55°	2.2	2.2	2.2	2.2	2.2
57.5°	1.9	1.9	1.9	1.9	1.9
60°	1.7	1.7	1.7	1.7	1.7
62.5°	1.5	1.5	1.5	1.5	1.5
65°	1.3	1.3	1.3	1.3	1.3
67.5°	1.3	1.3	1.3	1.3	1.3
70°	1.1	1.1	1.1	1.1	1.1
72.5°	0.9	0.9	0.9	0.9	0.9
75°	0.6	0.6	0.6	0.6	0.9
77.5°	0.6	0.6	0.6	0.6	0.6
80°	0.4	0.4	0.4	0.4	0.4
82.5°	0.4	0.4	0.4	0.4	0.4
85°	0.2	0.2	0.2	0.2	0.2
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)