

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786712

Luminaire Tested: LERS6D15D010-EC6DR350215IC9040-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D15D010-EC6DR350215IC9040-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2791.6 lumens
Efficiency: N/A
Efficacy: 176.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786712

CATALOG NUMBER: LERS6D15D010-EC6DR350215IC9040-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P786712

CATALOG NUMBER: LERS6D15D010-EC6DR350215IC9040-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96											96																	
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92											92																	
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88											88																	
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84											84																	
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81											81																	
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78											78																	
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75											75																	
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72											72																	
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70											70																	
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68											68																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	839265
5°	819537
10°	738625
15°	573290
20°	325157
25°	126499
30°	47198
35°	25863
40°	16902
45°	10291
50°	6544
55°	4629
60°	3387
65°	1836
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10291 cd/sqm



TEST NUMBER: P786712

CATALOG NUMBER: LERS6D15D010-EC6DR350215IC9040-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	687.2	24.6
10°-20°	1341.8	48.1
20°-30°	547.2	19.6
30°-40°	130.9	4.7
40°-50°	54.6	2.0
50°-60°	22.6	0.8
60°-70°	7.1	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2576.2	92.3
0°-40°	2707.2	97.0
0°-60°	2784.3	99.7
0°-90°	2791.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2791.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7681	
5°	7472	687
15°	5068	1342
25°	1049	547
35°	194	131
45°	67	55
55°	24	23
65°	7	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786712

CATALOG NUMBER: LERS6D15D010-EC6DR350215IC9040-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7681.3
2.5°	7635.2
5°	7472.2
7.5°	7147.2
10°	6657.5
12.5°	5968.0
15°	5068.2
17.5°	3967.8
20°	2796.5
22.5°	1783.2
25°	1049.3
27.5°	593.2
30°	374.1
32.5°	262.6
35°	193.9
37.5°	150.0
40°	118.5
42.5°	91.3
45°	66.6
47.5°	49.8
50°	38.5
52.5°	30.6
55°	24.3
57.5°	19.7
60°	15.5
62.5°	11.3
65°	7.1
67.5°	2.5
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)