

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785430

Luminaire Tested: LERS6D02D010-EC6DR300210IC9024-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P785430
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D02D010-EC6DR300210IC9024-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 595.7 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785430

CATALOG NUMBER: LERS6D02D010-EC6DR300210IC9024-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P785430

CATALOG NUMBER: LERS6D02D010-EC6DR300210IC9024-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	146611	146611	146611
5°	142407	142238	142407
10°	123341	122470	123317
15°	80472	80044	79640
20°	40019	41518	39962
25°	20160	22727	19746
30°	8070	8794	7035
35°	3747	3588	3009
40°	1619	1799	1519
45°	1137	1418	1147
50°	393	1036	417
55°	227	427	240
60°	153	184	153
65°	109	109	109
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 1418 cd/sqm



TEST NUMBER: P785430

CATALOG NUMBER: LERS6D02D010-EC6DR300210IC9024-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.4	28.3
10°-20°	271.3	45.5
20°-30°	117.2	19.7
30°-40°	26.7	4.5
40°-50°	9.2	1.5
50°-60°	2.2	0.4
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.9	93.5
0°-40°	583.6	98.0
0°-60°	595.0	99.9
0°-90°	595.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	595.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1915	1915	1915	1915	1915	
5°	1853	1852	1851	1855	1853	169
15°	1016	1003	1010	1007	1005	272
25°	239	248	269	241	234	114
35°	40	41	38	38	32	27
45°	10	13	13	13	11	7
55°	2	2	3	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P785430

CATALOG NUMBER: LERS6D02D010-EC6DR300210IC9024-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1915.4	1915.4	1915.4	1915.4	1915.4
2.5°	1902.7	1901.4	1902.2	1903.1	1903.5
5°	1853.4	1851.6	1851.2	1855.0	1853.4
7.5°	1753.8	1751.2	1747.4	1756.1	1764.3
10°	1586.9	1584.1	1575.7	1579.9	1586.6
12.5°	1340.6	1331.5	1331.3	1344.5	1342.7
15°	1015.5	1003.3	1010.1	1006.8	1005.0
17.5°	682.9	678.2	687.2	684.5	672.8
20°	491.3	492.5	509.7	501.0	490.6
22.5°	358.5	362.9	383.3	361.0	352.8
25°	238.7	247.7	269.1	241.4	233.8
27.5°	146.8	150.9	172.7	144.9	140.8
30°	91.3	89.2	99.5	85.4	79.6
32.5°	59.9	57.3	60.6	54.4	49.7
35°	40.1	40.9	38.4	38.1	32.2
37.5°	25.0	28.8	25.4	27.1	20.7
40°	16.2	20.9	18.0	19.8	15.2
42.5°	13.3	16.1	14.8	15.7	13.5
45°	10.5	13.1	13.1	13.1	10.6
47.5°	5.8	8.7	11.2	8.9	6.2
50°	3.3	4.4	8.7	4.6	3.5
52.5°	2.3	2.5	5.9	2.6	2.4
55°	1.7	1.8	3.2	1.9	1.8
57.5°	1.3	1.4	1.7	1.4	1.3
60°	1.0	1.0	1.2	1.1	1.0
62.5°	0.8	0.8	0.8	0.8	0.8
65°	0.6	0.6	0.6	0.6	0.6
67.5°	0.3	0.4	0.4	0.4	0.4
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)