

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786765

Luminaire Tested: LERS6D15D010-EC6DR500215IC9024-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D15D010-EC6DR500215IC9024-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2322.1 lumens
Efficiency: N/A
Efficacy: 147.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786765

CATALOG NUMBER: LERS6D15D010-EC6DR500215IC9024-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P786765

CATALOG NUMBER: LERS6D15D010-EC6DR500215IC9024-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95				95															
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90				90															
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				85															
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80				80															
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76				76															
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72				72															
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				69															
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65				65															
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62				62															
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59				59															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	408799
5°	404515
10°	397853
15°	362274
20°	301461
25°	213987
30°	113270
35°	46150
40°	17144
45°	7850
50°	3213
55°	1676
60°	830
65°	233
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7850 cd/sqm



TEST NUMBER: P786765

CATALOG NUMBER: LERS6D15D010-EC6DR500215IC9024-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.6	15.0
10°-20°	881.0	37.9
20°-30°	791.4	34.1
30°-40°	247.8	10.7
40°-50°	43.4	1.9
50°-60°	8.6	0.4
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2021.0	87.0
0°-40°	2268.8	97.7
0°-60°	2320.8	99.9
0°-90°	2322.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2322.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3742	
5°	3688	349
15°	3203	881
25°	1775	791
35°	346	248
45°	51	43
55°	9	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786765

CATALOG NUMBER: LERS6D15D010-EC6DR500215IC9024-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3741.5
2.5°	3722.9
5°	3688.2
7.5°	3635.2
10°	3586.0
12.5°	3428.3
15°	3202.7
17.5°	2916.3
20°	2592.7
22.5°	2218.2
25°	1775.0
27.5°	1305.0
30°	897.8
32.5°	584.5
35°	346.0
37.5°	198.7
40°	120.2
42.5°	78.2
45°	50.8
47.5°	30.9
50°	18.9
52.5°	12.9
55°	8.8
57.5°	6.0
60°	3.8
62.5°	2.2
65°	0.9
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)