

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786977

Luminaire Tested: LER6D02D010-EC6DR200210IC9024-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D02D010-EC6DR200210IC9024-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 351.8 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786977

CATALOG NUMBER: LER6D02D010-EC6DR200210IC9024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P786977

CATALOG NUMBER: LER6D02D010-EC6DR200210IC9024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	95	95	94															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	92	92	91															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	89	89	88															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	86	86	85															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	84	84	83															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	82	82	81															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	80	80	79															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	78	78	77															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	76	76	75															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	218806
5°	197399
10°	110791
15°	56320
20°	23848
25°	11007
30°	5829
35°	3134
40°	1683
45°	989
50°	578
55°	305
60°	197
65°	129
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 989 cd/sqm



TEST NUMBER: P786977

CATALOG NUMBER: LER6D02D010-EC6DR200210IC9024-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	40.5
10°-20°	140.4	39.9
20°-30°	45.9	13.0
30°-40°	15.6	4.4
40°-50°	5.3	1.5
50°-60°	1.6	0.4
60°-70°	0.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	328.9	93.5
0°-40°	344.5	97.9
0°-60°	351.3	99.8
0°-90°	351.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	351.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2003	
5°	1800	143
15°	498	140
25°	91	46
35°	24	16
45°	6	5
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786977

CATALOG NUMBER: LER6D02D010-EC6DR200210IC9024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2002.6
0.5°	2002.6
1°	2000.1
1.5°	1995.1
2°	1986.0
2.5°	1973.9
3°	1956.8
3.5°	1932.9
4°	1897.4
4.5°	1854.2
5°	1799.8
5.5°	1728.3
6°	1655.0
6.5°	1571.0
7°	1488.8
7.5°	1392.5
8°	1306.6
8.5°	1220.1
9°	1140.2
9.5°	1066.9
10°	998.6
12.5°	717.0
15°	497.9
17.5°	325.3
20°	205.1
22.5°	132.9
25°	91.3
27.5°	64.2
30°	46.2
32.5°	33.2
35°	23.5
37.5°	16.4
40°	11.8
42.5°	8.6
45°	6.4
47.5°	5.0
50°	3.4
52.5°	2.1
55°	1.6
57.5°	1.2
60°	0.9
62.5°	0.7
65°	0.5



TEST NUMBER: P786977

CATALOG NUMBER: LER6D02D010-EC6DR200210IC9024-6LBDP1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.4
70°		0.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)