

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787006

Luminaire Tested: LER6D02D010-EC6DR200210IC9035-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P787006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D02D010-EC6DR200210IC9035-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 405.4 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P787006
CATALOG NUMBER: LER6D02D010-EC6DR200210IC9035-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P787006

CATALOG NUMBER: LER6D02D010-EC6DR200210IC9035-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	94	94	94		
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	93	92	91	91	91		
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	90	89	88	88	88		
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	87	86	85	85	85		
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	84	83	82	82	82		
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	82	81	80	80	80		
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	80	79	78	78	78		
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	78	77	77	77	77		
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	76	75	75	75	75		
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	74	73	73	73	73		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252152
5°	227494
10°	127677
15°	64905
20°	27475
25°	12682
30°	6712
35°	3615
40°	1940
45°	1143
50°	663
55°	343
60°	219
65°	155
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1143 cd/sqm



TEST NUMBER: P787006

CATALOG NUMBER: LER6D02D010-EC6DR200210IC9035-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.3	40.5
10°-20°	161.8	39.9
20°-30°	52.9	13.0
30°-40°	18.0	4.4
40°-50°	6.1	1.5
50°-60°	1.8	0.4
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.0	93.5
0°-40°	396.9	97.9
0°-60°	404.8	99.8
0°-90°	405.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	405.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2308	
5°	2074	164
15°	574	162
25°	105	53
35°	27	18
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P787006

CATALOG NUMBER: LER6D02D010-EC6DR200210IC9035-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2307.8
0.5°	2307.8
1°	2304.9
1.5°	2299.2
2°	2288.7
2.5°	2274.7
3°	2255.0
3.5°	2227.5
4°	2186.6
4.5°	2136.8
5°	2074.2
5.5°	1991.7
6°	1907.3
6.5°	1810.5
7°	1715.8
7.5°	1604.8
8°	1505.7
8.5°	1406.1
9°	1314.0
9.5°	1229.5
10°	1150.8
12.5°	826.3
15°	573.8
17.5°	374.8
20°	236.3
22.5°	153.1
25°	105.2
27.5°	74.0
30°	53.2
32.5°	38.2
35°	27.1
37.5°	18.9
40°	13.6
42.5°	9.9
45°	7.4
47.5°	5.8
50°	3.9
52.5°	2.5
55°	1.8
57.5°	1.4
60°	1.0
62.5°	0.8
65°	0.6



TEST NUMBER: P787006

CATALOG NUMBER: LER6D02D010-EC6DR200210IC9035-6LBS1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.4
70°		0.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)