

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785749

Luminaire Tested: LERS6D05D010-EC6DR300210IC9030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P785749
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D05D010-EC6DR300210IC9030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1185.6 lumens
Efficiency: N/A
Efficacy: 158.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785749

CATALOG NUMBER: LERS6D05D010-EC6DR300210IC9030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P785749

CATALOG NUMBER: LERS6D05D010-EC6DR300210IC9030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	291799	291799	291799
5°	283424	283094	283432
10°	245484	243751	245430
15°	160167	159303	158503
20°	79647	82629	79533
25°	40117	45243	39298
30°	16060	17500	13991
35°	7447	7139	5980
40°	3217	3567	3028
45°	2273	2814	2284
50°	786	2048	822
55°	454	854	480
60°	321	367	321
65°	199	199	199
70°	134	90	134
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 2814 cd/sqm



TEST NUMBER: P785749

CATALOG NUMBER: LERS6D05D010-EC6DR300210IC9030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	335.2	28.3
10°-20°	539.9	45.5
20°-30°	233.3	19.7
30°-40°	53.2	4.5
40°-50°	18.3	1.5
50°-60°	4.5	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1108.4	93.5
0°-40°	1161.6	98.0
0°-60°	1184.3	99.9
0°-90°	1185.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1185.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3812	3812	3812	3812	3812	
5°	3689	3685	3684	3692	3689	335
15°	2021	1997	2010	2004	2000	541
25°	475	493	536	480	465	227
35°	80	81	76	76	64	54
45°	21	26	26	26	21	15
55°	3	4	6	4	4	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P785749

CATALOG NUMBER: LERS6D05D010-EC6DR300210IC9030-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3812.2	3812.2	3812.2	3812.2	3812.2
2.5°	3786.9	3784.3	3785.8	3787.7	3788.4
5°	3688.7	3685.1	3684.4	3692.0	3688.8
7.5°	3490.4	3485.4	3477.7	3495.1	3511.4
10°	3158.4	3152.8	3136.1	3144.4	3157.7
12.5°	2668.2	2650.1	2649.7	2675.9	2672.3
15°	2021.2	1996.9	2010.3	2003.8	2000.2
17.5°	1359.2	1349.8	1367.8	1362.4	1339.0
20°	977.8	980.2	1014.4	997.2	976.4
22.5°	713.5	722.3	762.9	718.5	702.2
25°	475.0	493.0	535.7	480.5	465.3
27.5°	292.2	300.4	343.6	288.4	280.2
30°	181.7	177.6	198.0	169.9	158.3
32.5°	119.2	114.0	120.5	108.2	98.8
35°	79.7	81.4	76.4	75.8	64.0
37.5°	49.8	57.3	50.5	53.9	41.2
40°	32.2	41.6	35.7	39.5	30.3
42.5°	26.4	32.0	29.4	31.3	27.0
45°	21.0	26.0	26.0	26.0	21.1
47.5°	11.6	17.4	22.3	17.8	12.4
50°	6.6	8.8	17.2	9.2	6.9
52.5°	4.5	5.1	11.8	5.2	4.7
55°	3.4	3.6	6.4	3.7	3.6
57.5°	2.6	2.8	3.4	2.8	2.6
60°	2.1	2.1	2.4	2.2	2.1
62.5°	1.5	1.5	1.7	1.5	1.5
65°	1.1	1.1	1.1	1.1	1.1
67.5°	0.6	0.7	0.7	0.7	0.7
70°	0.6	0.4	0.4	0.4	0.6
72.5°	0.4	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)