

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787110

Luminaire Tested: LER6D02D010-EC6DR300210IC9040-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P787110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D02D010-EC6DR300210IC9040-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 670.6 lumens
Efficiency: N/A
Efficacy: 131.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P787110
CATALOG NUMBER: LER6D02D010-EC6DR300210IC9040-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P787110

CATALOG NUMBER: LER6D02D010-EC6DR300210IC9040-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	165043	165043	165043
5°	160310	160118	160318
10°	138847	137867	138815
15°	90591	90108	89656
20°	45045	46739	44988
25°	22693	25590	22229
30°	9086	9899	7919
35°	4214	4037	3383
40°	1819	2018	1709
45°	1288	1591	1299
50°	441	1155	464
55°	254	480	267
60°	184	214	184
65°	109	109	109
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 1591 cd/sqm



TEST NUMBER: P787110

CATALOG NUMBER: LER6D02D010-EC6DR300210IC9040-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.6	28.3
10°-20°	305.4	45.5
20°-30°	132.0	19.7
30°-40°	30.1	4.5
40°-50°	10.3	1.5
50°-60°	2.5	0.4
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.9	93.5
0°-40°	657.0	98.0
0°-60°	669.9	99.9
0°-90°	670.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	670.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2156	2156	2156	2156	2156	
5°	2086	2084	2084	2088	2086	190
15°	1143	1130	1137	1133	1131	306
25°	269	279	303	272	263	129
35°	45	46	43	43	36	31
45°	12	15	15	15	12	8
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P787110

CATALOG NUMBER: LER6D02D010-EC6DR300210IC9040-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2156.2	2156.2	2156.2	2156.2	2156.2
2.5°	2141.9	2140.5	2141.3	2142.4	2142.8
5°	2086.4	2084.3	2083.9	2088.3	2086.5
7.5°	1974.2	1971.4	1967.0	1976.9	1986.1
10°	1786.4	1783.3	1773.8	1778.5	1786.0
12.5°	1509.2	1498.9	1498.7	1513.5	1511.5
15°	1143.2	1129.5	1137.1	1133.4	1131.4
17.5°	768.8	763.5	773.6	770.6	757.3
20°	553.0	554.4	573.8	564.0	552.3
22.5°	403.6	408.5	431.5	406.4	397.2
25°	268.7	278.8	303.0	271.8	263.2
27.5°	165.3	169.9	194.4	163.1	158.5
30°	102.8	100.5	112.0	96.1	89.6
32.5°	67.4	64.5	68.2	61.2	55.9
35°	45.1	46.1	43.2	42.9	36.2
37.5°	28.2	32.4	28.6	30.5	23.3
40°	18.2	23.5	20.2	22.3	17.1
42.5°	14.9	18.1	16.6	17.7	15.2
45°	11.9	14.7	14.7	14.7	12.0
47.5°	6.6	9.8	12.6	10.1	7.0
50°	3.7	5.0	9.7	5.2	3.9
52.5°	2.5	2.9	6.7	3.0	2.6
55°	1.9	2.0	3.6	2.1	2.0
57.5°	1.5	1.6	1.9	1.6	1.5
60°	1.2	1.2	1.4	1.3	1.2
62.5°	0.8	0.8	1.0	0.8	0.8
65°	0.6	0.6	0.6	0.6	0.6
67.5°	0.3	0.4	0.4	0.4	0.4
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)