

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787386

Luminaire Tested: LER6D02D010-EC6DR600210IC9035-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P787386  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D02D010-EC6DR600210IC9035-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 606.6 lumens  
Efficiency: N/A  
Efficacy: 118.9 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.84  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P787386

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9035-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P787386

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9035-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	78701
5°	80635
10°	81612
15°	77744
20°	68543
25°	55444
30°	37508
35°	18794
40°	3052
45°	2982
50°	3043
55°	3086
60°	3169
65°	3258
70°	3322
75°	3377
80°	3272
85°	2758

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 3377 cd/sqm



TEST NUMBER: P787386

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9035-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	11.6
10°-20°	190.1	31.3
20°-30°	204.5	33.7
30°-40°	88.9	14.7
40°-50°	14.9	2.5
50°-60°	14.5	2.4
60°-70°	12.4	2.0
70°-80°	8.3	1.4
80°-90°	2.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	464.9	76.6
0°-40°	553.8	91.3
0°-60°	583.3	96.2
0°-90°	606.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	720	
5°	735	70
15°	687	190
25°	460	205
35°	141	89
45°	19	15
55°	16	15
65°	13	12
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P787386

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9035-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	720.3
2.5°	740.6
5°	735.2
7.5°	736.9
10°	735.6
12.5°	720.4
15°	687.3
17.5°	642.9
20°	589.5
22.5°	532.4
25°	459.9
27.5°	367.8
30°	297.3
32.5°	229.1
35°	140.9
37.5°	60.3
40°	21.4
42.5°	19.7
45°	19.3
47.5°	18.7
50°	17.9
52.5°	17.1
55°	16.2
57.5°	15.4
60°	14.5
62.5°	13.6
65°	12.6
67.5°	11.5
70°	10.4
72.5°	9.2
75°	8.0
77.5°	6.6
80°	5.2
82.5°	3.7
85°	2.2
87.5°	0.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)