

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786006

Luminaire Tested: LERS6D08D010-EC6DR200210IC9024-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D08D010-EC6DR200210IC9024-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 794.3 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786006

CATALOG NUMBER: LERS6D08D010-EC6DR200210IC9024-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P786006

CATALOG NUMBER: LERS6D08D010-EC6DR200210IC9024-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97																	
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94																	
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91																	
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88																	
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85																	
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83																	
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81																	
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79																	
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77																	
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	494023
5°	445699
10°	250151
15°	127153
20°	53834
25°	24847
30°	13159
35°	7083
40°	3794
45°	2241
50°	1292
55°	686
60°	437
65°	310
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2241 cd/sqm



TEST NUMBER: P786006

CATALOG NUMBER: LERS6D08D010-EC6DR200210IC9024-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	321.9	40.5
10°-20°	317.0	39.9
20°-30°	103.6	13.0
30°-40°	35.2	4.4
40°-50°	11.9	1.5
50°-60°	3.5	0.4
60°-70°	1.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	742.5	93.5
0°-40°	777.7	97.9
0°-60°	793.1	99.8
0°-90°	794.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	794.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4522	
5°	4064	322
15°	1124	317
25°	206	104
35°	53	35
45°	14	12
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786006

CATALOG NUMBER: LERS6D08D010-EC6DR200210IC9024-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4521.5
0.5°	4521.5
1°	4515.8
1.5°	4504.6
2°	4484.0
2.5°	4456.7
3°	4418.0
3.5°	4364.1
4°	4283.9
4.5°	4186.5
5°	4063.7
5.5°	3902.2
6°	3736.8
6.5°	3547.1
7°	3361.5
7.5°	3144.1
8°	2950.0
8.5°	2754.8
9°	2574.4
9.5°	2408.9
10°	2254.7
12.5°	1619.0
15°	1124.1
17.5°	734.4
20°	463.0
22.5°	300.0
25°	206.1
27.5°	144.9
30°	104.3
32.5°	74.9
35°	53.1
37.5°	37.0
40°	26.6
42.5°	19.3
45°	14.5
47.5°	11.3
50°	7.6
52.5°	4.8
55°	3.6
57.5°	2.8
60°	2.0
62.5°	1.6
65°	1.2



TEST NUMBER: P786006

CATALOG NUMBER: LERS6D08D010-EC6DR200210IC9024-6LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.8
70°		0.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)