

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786054

Luminaire Tested: LERS6D08D010-EC6DR300210IC9024-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D08D010-EC6DR300210IC9024-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1277.7 lumens
Efficiency: N/A
Efficacy: 143.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786054

CATALOG NUMBER: LERS6D08D010-EC6DR300210IC9024-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P786054

CATALOG NUMBER: LERS6D08D010-EC6DR300210IC9024-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	314471	314471	314471
5°	305445	305092	305461
10°	264565	262700	264503
15°	172616	171689	170825
20°	85830	89056	85716
25°	43233	48757	42355
30°	17315	18861	15078
35°	8027	7690	6448
40°	3467	3847	3267
45°	2446	3031	2468
50°	845	2215	893
55°	480	921	507
60°	337	398	337
65°	217	217	217
70°	134	90	134
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 3031 cd/sqm



TEST NUMBER: P786054

CATALOG NUMBER: LERS6D08D010-EC6DR300210IC9024-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.3	28.3
10°-20°	581.8	45.5
20°-30°	251.4	19.7
30°-40°	57.3	4.5
40°-50°	19.7	1.5
50°-60°	4.8	0.4
60°-70°	1.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1194.5	93.5
0°-40°	1251.8	98.0
0°-60°	1276.3	99.9
0°-90°	1277.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1277.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4108	4108	4108	4108	4108	
5°	3975	3972	3971	3979	3976	362
15°	2178	2152	2167	2160	2156	583
25°	512	531	577	518	502	245
35°	86	88	82	82	69	58
45°	23	28	28	28	23	16
55°	4	4	7	4	4	4
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P786054

CATALOG NUMBER: LERS6D08D010-EC6DR300210IC9024-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4108.4	4108.4	4108.4	4108.4	4108.4
2.5°	4081.2	4078.4	4080.0	4082.0	4082.8
5°	3975.3	3971.5	3970.7	3978.9	3975.5
7.5°	3761.7	3756.2	3748.0	3766.7	3784.3
10°	3403.9	3397.8	3379.9	3388.7	3403.1
12.5°	2875.6	2856.0	2855.6	2883.9	2880.0
15°	2178.3	2152.0	2166.6	2159.5	2155.7
17.5°	1464.8	1454.7	1474.1	1468.2	1443.0
20°	1053.7	1056.4	1093.3	1074.7	1052.3
22.5°	768.9	778.4	822.2	774.4	756.8
25°	511.9	531.3	577.3	517.8	501.5
27.5°	314.9	323.7	370.3	310.8	302.0
30°	195.9	191.4	213.4	183.2	170.6
32.5°	128.5	122.8	129.9	116.6	106.5
35°	85.9	87.7	82.3	81.7	69.0
37.5°	53.7	61.7	54.5	58.1	44.4
40°	34.7	44.8	38.5	42.6	32.7
42.5°	28.4	34.5	31.7	33.7	29.0
45°	22.6	28.0	28.0	28.0	22.8
47.5°	12.5	18.8	24.0	19.2	13.3
50°	7.1	9.5	18.6	9.9	7.5
52.5°	4.8	5.4	12.7	5.6	5.0
55°	3.6	3.8	6.9	4.0	3.8
57.5°	2.8	3.0	3.6	3.0	2.8
60°	2.2	2.2	2.6	2.4	2.2
62.5°	1.6	1.6	1.8	1.6	1.6
65°	1.2	1.2	1.2	1.2	1.2
67.5°	0.6	0.8	0.8	0.8	0.8
70°	0.6	0.4	0.4	0.4	0.6
72.5°	0.4	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)