

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787451

Luminaire Tested: LER6D02D010-EC6DR650210IC9050-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P787451  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D02D010-EC6DR650210IC9050-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 580.8 lumens  
Efficiency: N/A  
Efficacy: 113.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P787451  
CATALOG NUMBER: LER6D02D010-EC6DR650210IC9050-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P787451

CATALOG NUMBER: LER6D02D010-EC6DR650210IC9050-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	30796
5°	30721
10°	30696
15°	29748
20°	27086
25°	23598
30°	19631
35°	15550
40°	11223
45°	7095
50°	3698
55°	1965
60°	1028
65°	567
70°	239
75°	271
80°	168
85°	134

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7095 cd/sqm



TEST NUMBER: P787451

CATALOG NUMBER: LER6D02D010-EC6DR650210IC9050-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.9	8.6
10°-20°	136.6	23.5
20°-30°	166.9	28.7
30°-40°	135.4	23.3
40°-50°	67.5	11.6
50°-60°	18.8	3.2
60°-70°	4.3	0.7
70°-80°	1.1	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.4	60.8
0°-40°	488.8	84.2
0°-60°	575.1	99.0
0°-90°	580.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	580.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	527	
5°	524	50
15°	492	137
25°	366	167
35°	218	135
45°	86	67
55°	19	19
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P787451

CATALOG NUMBER: LER6D02D010-EC6DR650210IC9050-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	527.3
2.5°	527.0
5°	524.0
7.5°	522.3
10°	517.6
12.5°	508.0
15°	492.0
17.5°	467.1
20°	435.8
22.5°	402.0
25°	366.2
27.5°	328.0
30°	291.1
32.5°	254.6
35°	218.1
37.5°	181.8
40°	147.2
42.5°	114.8
45°	85.9
47.5°	59.8
50°	40.7
52.5°	28.1
55°	19.3
57.5°	13.0
60°	8.8
62.5°	6.1
65°	4.1
67.5°	2.1
70°	1.4
72.5°	1.3
75°	1.2
77.5°	0.8
80°	0.5
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)