

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787480

Luminaire Tested: LER6D02D010-EC6DR700210IC9035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P787480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D02D010-EC6DR700210IC9035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 674.1 lumens
Efficiency: N/A
Efficacy: 132.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P787480

CATALOG NUMBER: LER6D02D010-EC6DR700210IC9035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P787480

CATALOG NUMBER: LER6D02D010-EC6DR700210IC9035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82809
5°	80350
10°	78106
15°	77088
20°	71985
25°	54069
30°	38228
35°	13538
40°	7117
45°	7587
50°	7853
55°	8001
60°	8042
65°	7885
70°	7443
75°	6881
80°	6103
85°	5015

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 8053 cd/sqm



TEST NUMBER: P787480

CATALOG NUMBER: LER6D02D010-EC6DR700210IC9035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	10.3
10°-20°	189.5	28.1
20°-30°	208.7	31.0
30°-40°	79.7	11.8
40°-50°	37.7	5.6
50°-60°	37.4	5.6
60°-70°	30.0	4.4
70°-80°	17.2	2.6
80°-90°	4.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	467.4	69.3
0°-40°	547.1	81.2
0°-60°	622.2	92.3
0°-90°	674.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	674.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	758	
5°	733	69
15°	682	190
25°	448	209
35°	102	80
45°	49	38
55°	42	37
65°	30	30
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P787480

CATALOG NUMBER: LER6D02D010-EC6DR700210IC9035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	757.9
2.5°	750.0
5°	732.6
7.5°	718.1
10°	704.0
12.5°	692.1
15°	681.5
17.5°	655.7
20°	619.1
22.5°	540.1
25°	448.5
27.5°	390.5
30°	303.0
32.5°	195.7
35°	101.5
37.5°	54.8
40°	49.9
42.5°	49.6
45°	49.1
47.5°	48.0
50°	46.2
52.5°	44.2
55°	42.0
57.5°	39.6
60°	36.8
62.5°	33.7
65°	30.5
67.5°	26.9
70°	23.3
72.5°	19.7
75°	16.3
77.5°	12.8
80°	9.7
82.5°	6.8
85°	4.0
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)