

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786087

Luminaire Tested: LERS6D08D010-EC6DR350210IC9030-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P786087  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LERS6D08D010-EC6DR350210IC9030-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1296.9 lumens  
Efficiency: N/A  
Efficacy: 145.7 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P786087

CATALOG NUMBER: LERS6D08D010-EC6DR350210IC9030-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P786087

CATALOG NUMBER: LERS6D08D010-EC6DR350210IC9030-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																											
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96									96																											
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92									92																											
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88									88																											
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84									84																											
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81									81																											
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78									78																											
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75									75																											
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72									72																											
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70									70																											
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68									68																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	389875
5°	380715
10°	343124
15°	266318
20°	151050
25°	58771
30°	21927
35°	12018
40°	7859
45°	4775
50°	3043
55°	2153
60°	1573
65°	853
70°	64
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4775 cd/sqm



TEST NUMBER: P786087

CATALOG NUMBER: LERS6D08D010-EC6DR350210IC9030-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	319.2	24.6
10°-20°	623.3	48.1
20°-30°	254.2	19.6
30°-40°	60.8	4.7
40°-50°	25.4	2.0
50°-60°	10.5	0.8
60°-70°	3.3	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1196.8	92.3
0°-40°	1257.6	97.0
0°-60°	1293.4	99.7
0°-90°	1296.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1296.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3568	
5°	3471	319
15°	2354	623
25°	488	254
35°	90	61
45°	31	25
55°	11	10
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786087

CATALOG NUMBER: LERS6D08D010-EC6DR350210IC9030-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3568.3
2.5°	3546.9
5°	3471.2
7.5°	3320.2
10°	3092.7
12.5°	2772.4
15°	2354.4
17.5°	1843.2
20°	1299.1
22.5°	828.4
25°	487.5
27.5°	275.5
30°	173.8
32.5°	122.0
35°	90.1
37.5°	69.7
40°	55.1
42.5°	42.4
45°	30.9
47.5°	23.2
50°	17.9
52.5°	14.2
55°	11.3
57.5°	9.1
60°	7.2
62.5°	5.3
65°	3.3
67.5°	1.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)