

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787599

Luminaire Tested: LER6D05D010-EC6DR200210IC9024-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P787599
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D05D010-EC6DR200210IC9024-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 523.7 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P787599

CATALOG NUMBER: LER6D05D010-EC6DR200210IC9024-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P787599

CATALOG NUMBER: LER6D05D010-EC6DR200210IC9024-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	95															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	96	94	93															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	94	92	91															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	92	90	89															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	90	88	87															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	88	86	85															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	86	84	83															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	84	82	81															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	325674
5°	293817
10°	164911
15°	83830
20°	35486
25°	16384
30°	8667
35°	4668
40°	2496
45°	1483
50°	850
55°	457
60°	284
65°	207
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1483 cd/sqm



TEST NUMBER: P787599

CATALOG NUMBER: LER6D05D010-EC6DR200210IC9024-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.2	40.5
10°-20°	209.0	39.9
20°-30°	68.3	13.0
30°-40°	23.2	4.4
40°-50°	7.8	1.5
50°-60°	2.4	0.5
60°-70°	0.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.5	93.5
0°-40°	512.7	97.9
0°-60°	522.9	99.8
0°-90°	523.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	523.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2981	
5°	2679	212
15°	741	209
25°	136	68
35°	35	23
45°	10	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P787599

CATALOG NUMBER: LER6D05D010-EC6DR200210IC9024-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2980.7
0.5°	2980.7
1°	2977.0
1.5°	2969.6
2°	2956.0
2.5°	2938.0
3°	2912.5
3.5°	2877.0
4°	2824.1
4.5°	2759.9
5°	2678.9
5.5°	2572.5
6°	2463.4
6.5°	2338.4
7°	2216.0
7.5°	2072.7
8°	1944.8
8.5°	1816.0
9°	1697.1
9.5°	1588.0
10°	1486.4
12.5°	1067.3
15°	741.1
17.5°	484.1
20°	305.2
22.5°	197.7
25°	135.9
27.5°	95.6
30°	68.7
32.5°	49.4
35°	35.0
37.5°	24.4
40°	17.5
42.5°	12.7
45°	9.6
47.5°	7.4
50°	5.0
52.5°	3.2
55°	2.4
57.5°	1.9
60°	1.3
62.5°	1.1
65°	0.8



TEST NUMBER: P787599

CATALOG NUMBER: LER6D05D010-EC6DR200210IC9024-6LBDP1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.5
70°		0.3

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)