

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787735

Luminaire Tested: LER6D05D010-EC6DR300210IC9050-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P787735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D05D010-EC6DR300210IC9050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 972.1 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P787735

CATALOG NUMBER: LER6D05D010-EC6DR300210IC9050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P787735

CATALOG NUMBER: LER6D05D010-EC6DR300210IC9050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	239259	239259	239259
5°	232397	232121	232405
10°	201290	199868	201244
15°	131330	130625	129967
20°	65303	67755	65213
25°	32896	37093	32220
30°	13169	14354	11472
35°	6111	5849	4906
40°	2638	2928	2488
45°	1862	2306	1873
50°	643	1679	679
55°	374	694	387
60°	260	306	260
65°	163	163	163
70°	112	67	112
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 2306 cd/sqm



TEST NUMBER: P787735

CATALOG NUMBER: LER6D05D010-EC6DR300210IC9050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.9	28.3
10°-20°	442.7	45.5
20°-30°	191.3	19.7
30°-40°	43.6	4.5
40°-50°	15.0	1.5
50°-60°	3.7	0.4
60°-70°	0.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	908.8	93.5
0°-40°	952.4	98.0
0°-60°	971.1	99.9
0°-90°	972.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	972.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3126	3126	3126	3126	3126	
5°	3025	3022	3021	3027	3025	275
15°	1657	1637	1648	1643	1640	444
25°	390	404	439	394	382	186
35°	65	67	63	62	52	44
45°	17	21	21	21	17	12
55°	3	3	5	3	3	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P787735

CATALOG NUMBER: LER6D05D010-EC6DR300210IC9050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3125.8	3125.8	3125.8	3125.8	3125.8
2.5°	3105.1	3103.0	3104.2	3105.7	3106.4
5°	3024.6	3021.6	3021.0	3027.3	3024.7
7.5°	2862.0	2857.9	2851.6	2865.9	2879.2
10°	2589.8	2585.2	2571.5	2578.3	2589.2
12.5°	2187.8	2173.0	2172.7	2194.1	2191.2
15°	1657.3	1637.4	1648.4	1643.0	1640.1
17.5°	1114.5	1106.8	1121.5	1117.1	1097.9
20°	801.7	803.7	831.8	817.7	800.6
22.5°	585.0	592.2	625.5	589.2	575.8
25°	389.5	404.2	439.2	394.0	381.5
27.5°	239.6	246.3	281.8	236.5	229.7
30°	149.0	145.6	162.4	139.3	129.8
32.5°	97.8	93.5	98.8	88.7	81.0
35°	65.4	66.8	62.6	62.2	52.5
37.5°	40.8	47.0	41.4	44.2	33.8
40°	26.4	34.1	29.3	32.4	24.9
42.5°	21.6	26.2	24.1	25.6	22.1
45°	17.2	21.3	21.3	21.3	17.3
47.5°	9.5	14.3	18.3	14.6	10.1
50°	5.4	7.2	14.1	7.5	5.7
52.5°	3.7	4.1	9.7	4.3	3.8
55°	2.8	2.9	5.2	3.1	2.9
57.5°	2.1	2.3	2.8	2.3	2.1
60°	1.7	1.7	2.0	1.8	1.7
62.5°	1.2	1.2	1.4	1.2	1.2
65°	0.9	0.9	0.9	0.9	0.9
67.5°	0.5	0.6	0.6	0.6	0.6
70°	0.5	0.3	0.3	0.3	0.5
72.5°	0.3	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)