

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786300

Luminaire Tested: LERS6D10D010-EC6DR150210IC9030-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P786300  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LERS6D10D010-EC6DR150210IC9030-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1037.1 lumens  
Efficiency: N/A  
Efficacy: 88.6 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P786300

CATALOG NUMBER: LERS6D10D010-EC6DR150210IC9030-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P786300

CATALOG NUMBER: LERS6D10D010-EC6DR150210IC9030-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1589828	1589828	1589828
5°	934254	922160	929457
10°	278831	280781	285083
15°	69355	70710	68521
20°	20750	24031	21192
25°	7315	9317	7408
30°	2688	3542	2733
35°	1343	1518	1300
40°	852	937	852
45°	630	672	630
50°	501	501	501
55°	418	418	418
60°	337	337	337
65°	257	257	257
70°	219	219	219
75°	136	136	181
80°	95	95	95
85°	50	50	50

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 672 cd/sqm



TEST NUMBER: P786300

CATALOG NUMBER: LERS6D10D010-EC6DR150210IC9030-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	672.6	64.9
10°-20°	276.7	26.7
20°-30°	55.0	5.3
30°-40°	13.7	1.3
40°-50°	7.2	0.7
50°-60°	5.4	0.5
60°-70°	3.8	0.4
70°-80°	2.2	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1004.2	96.8
0°-40°	1017.9	98.1
0°-60°	1030.5	99.4
0°-90°	1037.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1037.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	14129	14129	14129	14129	14129	
5°	9193	9098	9074	9137	9146	671
15°	798	814	814	800	789	274
25°	94	106	120	106	95	49
35°	18	20	21	20	18	13
45°	9	9	10	9	9	7
55°	6	6	6	6	6	5
65°	4	4	4	4	4	4
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P786300

CATALOG NUMBER: LERS6D10D010-EC6DR150210IC9030-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	14129.3	14129.3	14129.3	14129.3	14129.3
2.5°	12745.2	12755.9	12760.1	12772.7	12819.3
5°	9192.8	9098.3	9073.8	9136.6	9145.6
7.5°	5445.5	5464.6	5534.6	5550.1	5493.9
10°	2988.3	3012.8	3009.2	3030.8	3055.3
12.5°	1528.2	1509.1	1503.1	1527.6	1493.6
15°	798.5	813.5	814.1	799.7	788.9
17.5°	429.5	446.8	475.5	452.2	416.3
20°	253.6	269.2	293.7	274.5	259.0
22.5°	156.7	169.3	186.6	171.7	159.1
25°	93.9	106.5	119.6	105.9	95.1
27.5°	55.6	66.4	74.8	65.8	55.0
30°	35.9	41.9	47.3	41.3	36.5
32.5°	25.1	27.5	29.9	27.5	25.1
35°	18.5	19.7	20.9	19.7	17.9
37.5°	14.4	15.6	16.1	15.0	13.8
40°	12.0	12.6	13.2	12.6	12.0
42.5°	10.2	10.8	10.8	10.8	10.2
45°	9.0	9.0	9.6	9.0	9.0
47.5°	7.8	7.8	8.4	7.8	7.8
50°	7.2	7.2	7.2	7.2	7.2
52.5°	6.6	6.6	6.6	6.6	6.6
55°	6.0	6.0	6.0	6.0	6.0
57.5°	5.4	5.4	5.4	5.4	5.4
60°	4.8	4.8	4.8	4.8	4.8
62.5°	4.2	4.2	4.2	4.2	4.2
65°	3.6	3.6	3.6	3.6	3.6
67.5°	3.6	3.6	3.6	3.6	3.6
70°	3.0	3.0	3.0	3.0	3.0
72.5°	2.4	2.4	2.4	2.4	2.4
75°	1.8	1.8	1.8	1.8	2.4
77.5°	1.8	1.8	1.8	1.8	1.8
80°	1.2	1.2	1.2	1.2	1.2
82.5°	1.2	1.2	1.2	1.2	1.2
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)