

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786333

Luminaire Tested: LERS6D10D010-EC6DR200210IC9040-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P786333  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LERS6D10D010-EC6DR200210IC9040-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1257.7 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P786333

CATALOG NUMBER: LERS6D10D010-EC6DR200210IC9040-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P786333

CATALOG NUMBER: LERS6D10D010-EC6DR200210IC9040-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	782154
5°	705647
10°	396045
15°	201322
20°	85240
25°	39349
30°	20830
35°	11217
40°	6005
45°	3538
50°	2057
55°	1086
60°	699
65°	491
70°	192
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3538 cd/sqm



TEST NUMBER: P786333

CATALOG NUMBER: LERS6D10D010-EC6DR200210IC9040-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	509.7	40.5
10°-20°	501.9	39.9
20°-30°	164.0	13.0
30°-40°	55.8	4.4
40°-50°	18.8	1.5
50°-60°	5.6	0.4
60°-70°	1.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1175.5	93.5
0°-40°	1231.3	97.9
0°-60°	1255.7	99.8
0°-90°	1257.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1257.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7159	
5°	6434	510
15°	1780	502
25°	326	164
35°	84	56
45°	23	19
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786333

CATALOG NUMBER: LERS6D10D010-EC6DR200210IC9040-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7158.6
0.5°	7158.6
1°	7149.7
1.5°	7131.8
2°	7099.3
2.5°	7056.0
3°	6994.8
3.5°	6909.3
4°	6782.5
4.5°	6628.2
5°	6433.8
5.5°	6178.2
6°	5916.2
6.5°	5616.0
7°	5322.1
7.5°	4977.9
8°	4670.6
8.5°	4361.4
9°	4075.9
9.5°	3813.9
10°	3569.7
12.5°	2563.2
15°	1779.8
17.5°	1162.7
20°	733.1
22.5°	474.9
25°	326.4
27.5°	229.5
30°	165.1
32.5°	118.6
35°	84.1
37.5°	58.6
40°	42.1
42.5°	30.6
45°	22.9
47.5°	17.8
50°	12.1
52.5°	7.6
55°	5.7
57.5°	4.5
60°	3.2
62.5°	2.5
65°	1.9



TEST NUMBER: P786333

CATALOG NUMBER: LERS6D10D010-EC6DR200210IC9040-6LBS1H

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.3
70°		0.6

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)