

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786376

Luminaire Tested: LERS6D10D010-EC6DR300210IC9035-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D10D010-EC6DR300210IC9035-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1845.6 lumens
Efficiency: N/A
Efficacy: 157.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786376

CATALOG NUMBER: LERS6D10D010-EC6DR300210IC9035-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P786376

CATALOG NUMBER: LERS6D10D010-EC6DR300210IC9035-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96	96	96		
	2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92	92	92	92	92	92		
	3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89	89	89	89	89	89		
	4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85	85	85	85	85	85		
	5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82	82	82	82	82	82		
	6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79	79	79	79	79	79		
	7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77	77	77	77	77	77		
	8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74	74	74	74	74	74		
	9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72	72	72	72	72	72		
	10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69	69	69	69	69	69		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	454247	454247	454247
5°	441206	440692	441229
10°	382154	379457	382061
15°	249340	248001	246749
20°	123984	128635	123821
25°	62455	70428	61172
30°	25004	27249	21787
35°	11596	11110	9307
40°	5006	5566	4716
45°	3529	4384	3561
50°	1215	3191	1286
55°	694	1321	734
60°	490	582	490
65°	308	308	308
70°	201	134	201
75°	0	89	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 4384 cd/sqm



TEST NUMBER: P786376

CATALOG NUMBER: LERS6D10D010-EC6DR300210IC9035-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	521.9	28.3
10°-20°	840.4	45.5
20°-30°	363.2	19.7
30°-40°	82.8	4.5
40°-50°	28.4	1.5
50°-60°	6.9	0.4
60°-70°	1.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1725.5	93.5
0°-40°	1808.3	98.0
0°-60°	1843.6	99.9
0°-90°	1845.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1845.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5934	5934	5934	5934	5934	
5°	5742	5737	5736	5748	5742	522
15°	3146	3109	3130	3119	3114	843
25°	740	768	834	748	724	354
35°	124	127	119	118	100	84
45°	33	40	40	40	33	23
55°	5	6	10	6	6	5
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P786376

CATALOG NUMBER: LERS6D10D010-EC6DR300210IC9035-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5934.5	5934.5	5934.5	5934.5	5934.5
2.5°	5895.2	5891.1	5893.4	5896.4	5897.5
5°	5742.2	5736.7	5735.5	5747.5	5742.5
7.5°	5433.7	5425.8	5413.9	5441.0	5466.3
10°	4916.8	4908.0	4882.1	4894.9	4915.6
12.5°	4153.7	4125.4	4124.9	4165.6	4160.1
15°	3146.5	3108.6	3129.6	3119.4	3113.8
17.5°	2115.9	2101.3	2129.3	2120.8	2084.4
20°	1522.1	1525.9	1579.2	1552.4	1520.1
22.5°	1110.7	1124.4	1187.6	1118.6	1093.2
25°	739.5	767.5	833.9	747.9	724.3
27.5°	454.8	467.6	534.9	449.0	436.2
30°	282.9	276.5	308.3	264.6	246.5
32.5°	185.6	177.4	187.6	168.4	153.8
35°	124.1	126.7	118.9	118.0	99.6
37.5°	77.5	89.2	78.7	83.9	64.1
40°	50.1	64.7	55.7	61.5	47.2
42.5°	41.1	49.8	45.7	48.7	42.0
45°	32.6	40.5	40.5	40.5	32.9
47.5°	18.1	27.1	34.7	27.7	19.2
50°	10.2	13.7	26.8	14.3	10.8
52.5°	7.0	7.9	18.4	8.2	7.3
55°	5.2	5.5	9.9	5.8	5.5
57.5°	4.1	4.4	5.2	4.4	4.1
60°	3.2	3.2	3.8	3.5	3.2
62.5°	2.3	2.3	2.6	2.3	2.3
65°	1.7	1.7	1.7	1.7	1.7
67.5°	0.9	1.2	1.2	1.2	1.2
70°	0.9	0.6	0.6	0.6	0.9
72.5°	0.6	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)