

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788080

Luminaire Tested: LER6D05D010-EC6DR700210IC9024-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788080  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D05D010-EC6DR700210IC9024-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1015.7 lumens  
Efficiency: N/A  
Efficacy: 135.4 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P788080  
CATALOG NUMBER: LER6D05D010-EC6DR700210IC9024-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P788080

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9024-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	124765
5°	121063
10°	117692
15°	116147
20°	108459
25°	81472
30°	57594
35°	20408
40°	10726
45°	11419
50°	11831
55°	12058
60°	12128
65°	11867
70°	11213
75°	10385
80°	9186
85°	7522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 12140 cd/sqm



TEST NUMBER: P788080

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9024-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.1	10.3
10°-20°	285.6	28.1
20°-30°	314.5	31.0
30°-40°	120.2	11.8
40°-50°	56.7	5.6
50°-60°	56.4	5.6
60°-70°	45.2	4.4
70°-80°	26.0	2.6
80°-90°	7.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	704.2	69.3
0°-40°	824.4	81.2
0°-60°	937.5	92.3
0°-90°	1015.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1015.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1142	
5°	1104	104
15°	1027	286
25°	676	315
35°	153	120
45°	74	57
55°	63	56
65°	46	45
75°	25	26
85°	6	7
90°	0	



TEST NUMBER: P788080

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9024-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1141.9
2.5°	1130.0
5°	1103.8
7.5°	1081.9
10°	1060.8
12.5°	1042.9
15°	1026.8
17.5°	987.9
20°	932.8
22.5°	813.8
25°	675.8
27.5°	588.3
30°	456.5
32.5°	294.9
35°	153.0
37.5°	82.6
40°	75.2
42.5°	74.7
45°	73.9
47.5°	72.3
50°	69.6
52.5°	66.5
55°	63.3
57.5°	59.7
60°	55.5
62.5°	50.8
65°	45.9
67.5°	40.5
70°	35.1
72.5°	29.7
75°	24.6
77.5°	19.3
80°	14.6
82.5°	10.3
85°	6.0
87.5°	2.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)