

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788092

Luminaire Tested: LER6D05D010-EC6DR700210IC9027-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788092  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D05D010-EC6DR700210IC9027-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1186.9 lumens  
Efficiency: N/A  
Efficacy: 158.3 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P788092

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9027-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P788092

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9027-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |   |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 95  | 94  | 93  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 107 | 102 | 97  | 94  | 105 | 100 | 96  | 92  | 97  | 93  | 90  | 94  | 91  | 88  | 91  | 89  | 87  | 85  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 85  | 82  | 87  | 84  | 81  | 85  | 82  | 79  | 78  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 95  | 87  | 81  | 76  | 93  | 86  | 80  | 76  | 83  | 78  | 75  | 81  | 77  | 74  | 79  | 76  | 73  | 71  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 89  | 80  | 74  | 69  | 88  | 79  | 73  | 69  | 78  | 72  | 68  | 76  | 71  | 68  | 74  | 70  | 67  | 65  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 84  | 75  | 68  | 63  | 83  | 74  | 68  | 63  | 72  | 67  | 63  | 71  | 66  | 62  | 69  | 65  | 62  | 60  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 62  | 58  | 67  | 62  | 58  | 66  | 61  | 57  | 65  | 61  | 57  | 56  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 75  | 65  | 58  | 54  | 74  | 64  | 58  | 54  | 63  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 51  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 71  | 61  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 50  | 58  | 53  | 49  | 57  | 53  | 49  | 48  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 67  | 57  | 50  | 46  | 66  | 56  | 50  | 46  | 55  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 46  | 44  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 102355 |
| 5°  | 102099 |
| 10° | 101871 |
| 15° | 101849 |
| 20° | 100855 |
| 25° | 94733  |
| 30° | 84454  |
| 35° | 67345  |
| 40° | 44714  |
| 45° | 26732  |
| 50° | 13853  |
| 55° | 7277   |
| 60° | 2579   |
| 65° | 52     |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26732 cd/sqm



TEST NUMBER: P788092

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9027-6LBS1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 88.5   | 7.5       |
| 10°-20°   | 253.9  | 21.4      |
| 20°-30°   | 358.2  | 30.2      |
| 30°-40°   | 309.2  | 26.1      |
| 40°-50°   | 138.5  | 11.7      |
| 50°-60°   | 36.3   | 3.1       |
| 60°-70°   | 2.4    | 0.2       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 700.6  | 59.0      |
| 0°-40°    | 1009.8 | 85.1      |
| 0°-60°    | 1184.5 | 99.8      |
| 0°-90°    | 1186.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1186.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 937 |      |
| 5°  | 931 | 89   |
| 15° | 900 | 254  |
| 25° | 786 | 358  |
| 35° | 505 | 309  |
| 45° | 173 | 138  |
| 55° | 38  | 36   |
| 65° | 0   | 2    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P788092

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9027-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 936.8 |
| 2.5°  | 935.8 |
| 5°    | 930.9 |
| 7.5°  | 926.8 |
| 10°   | 918.2 |
| 12.5° | 910.5 |
| 15°   | 900.4 |
| 17.5° | 888.8 |
| 20°   | 867.4 |
| 22.5° | 832.2 |
| 25°   | 785.8 |
| 27.5° | 732.1 |
| 30°   | 669.4 |
| 32.5° | 592.8 |
| 35°   | 504.9 |
| 37.5° | 407.8 |
| 40°   | 313.5 |
| 42.5° | 238.2 |
| 45°   | 173.0 |
| 47.5° | 119.3 |
| 50°   | 81.5  |
| 52.5° | 56.3  |
| 55°   | 38.2  |
| 57.5° | 23.1  |
| 60°   | 11.8  |
| 62.5° | 3.7   |
| 65°   | 0.2   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)