

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786554

Luminaire Tested: LERS6D10D010-EC6DR650210IC9050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D10D010-EC6DR650210IC9050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1883.5 lumens
Efficiency: N/A
Efficacy: 161.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786554

CATALOG NUMBER: LERS6D10D010-EC6DR650210IC9050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P786554

CATALOG NUMBER: LERS6D10D010-EC6DR650210IC9050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99876
5°	99625
10°	99543
15°	96471
20°	87827
25°	76537
30°	63656
35°	50436
40°	36405
45°	22995
50°	11984
55°	6374
60°	3341
65°	1838
70°	768
75°	857
80°	605
85°	536

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22995 cd/sqm



TEST NUMBER: P786554

CATALOG NUMBER: LERS6D10D010-EC6DR650210IC9050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.7	8.6
10°-20°	442.9	23.5
20°-30°	541.3	28.7
30°-40°	439.2	23.3
40°-50°	218.9	11.6
50°-60°	61.0	3.2
60°-70°	13.9	0.7
70°-80°	3.6	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1145.9	60.8
0°-40°	1585.1	84.2
0°-60°	1865.0	99.0
0°-90°	1883.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1883.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1710	
5°	1699	162
15°	1596	443
25°	1188	541
35°	707	439
45°	278	219
55°	63	61
65°	13	14
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P786554

CATALOG NUMBER: LERS6D10D010-EC6DR650210IC9050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1710.1
2.5°	1708.9
5°	1699.3
7.5°	1693.8
10°	1678.5
12.5°	1647.3
15°	1595.5
17.5°	1514.6
20°	1413.1
22.5°	1303.5
25°	1187.7
27.5°	1063.8
30°	943.9
32.5°	825.5
35°	707.4
37.5°	589.6
40°	477.5
42.5°	372.4
45°	278.4
47.5°	194.0
50°	131.9
52.5°	91.0
55°	62.6
57.5°	42.2
60°	28.6
62.5°	19.9
65°	13.3
67.5°	6.8
70°	4.5
72.5°	4.3
75°	3.8
77.5°	2.5
80°	1.8
82.5°	1.3
85°	0.8
87.5°	0.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)