

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788113

Luminaire Tested: LER6D05D010-EC6DR700210IC9040-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788113  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D05D010-EC6DR700210IC9040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1326.2 lumens  
Efficiency: N/A  
Efficacy: 176.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P788113

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P788113

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	162908
5°	158068
10°	153661
15°	151642
20°	141609
25°	106379
30°	75206
35°	26637
40°	14006
45°	14926
50°	15451
55°	15734
60°	15843
65°	15512
70°	14631
75°	13551
80°	12018
85°	9778

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 15843 cd/sqm



TEST NUMBER: P788113

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9040-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.9	10.2
10°-20°	372.9	28.1
20°-30°	410.7	31.0
30°-40°	156.9	11.8
40°-50°	74.1	5.6
50°-60°	73.7	5.6
60°-70°	59.0	4.4
70°-80°	33.9	2.6
80°-90°	9.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	919.5	69.3
0°-40°	1076.4	81.2
0°-60°	1224.1	92.3
0°-90°	1326.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1326.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1491	
5°	1441	136
15°	1341	373
25°	882	411
35°	200	157
45°	97	74
55°	83	74
65°	60	59
75°	32	34
85°	8	9
90°	0	



TEST NUMBER: P788113

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1491.0
2.5°	1475.4
5°	1441.2
7.5°	1412.6
10°	1385.0
12.5°	1361.6
15°	1340.6
17.5°	1289.9
20°	1217.9
22.5°	1062.5
25°	882.4
27.5°	768.2
30°	596.1
32.5°	385.0
35°	199.7
37.5°	107.9
40°	98.2
42.5°	97.5
45°	96.6
47.5°	94.4
50°	90.9
52.5°	86.9
55°	82.6
57.5°	77.9
60°	72.5
62.5°	66.3
65°	60.0
67.5°	52.9
70°	45.8
72.5°	38.7
75°	32.1
77.5°	25.3
80°	19.1
82.5°	13.5
85°	7.8
87.5°	3.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)