

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786577

Luminaire Tested: LERS6D10D010-EC6DR700210IC9050-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D10D010-EC6DR700210IC9050-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2066.4 lumens
Efficiency: N/A
Efficacy: 176.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786577

CATALOG NUMBER: LERS6D10D010-EC6DR700210IC9050-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P786577

CATALOG NUMBER: LERS6D10D010-EC6DR700210IC9050-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 95 | 94 | 93 | | | | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 92 | 97 | 93 | 90 | 94 | 91 | 88 | 91 | 89 | 87 | 85 | | | | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 85 | 82 | 87 | 84 | 81 | 85 | 82 | 79 | 78 | | | | | | | | | | | | | | | | | | | |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 83 | 78 | 75 | 81 | 77 | 74 | 79 | 76 | 73 | 71 | | | | | | | | | | | | | | | | | | | |
| 5 | 89 | 80 | 74 | 69 | 88 | 79 | 73 | 69 | 78 | 72 | 68 | 76 | 71 | 68 | 74 | 70 | 67 | 65 | | | | | | | | | | | | | | | | | | | |
| 6 | 84 | 75 | 68 | 63 | 83 | 74 | 68 | 63 | 72 | 67 | 63 | 71 | 66 | 62 | 69 | 65 | 62 | 60 | | | | | | | | | | | | | | | | | | | |
| 7 | 80 | 69 | 63 | 58 | 78 | 69 | 62 | 58 | 67 | 62 | 58 | 66 | 61 | 57 | 65 | 61 | 57 | 56 | | | | | | | | | | | | | | | | | | | |
| 8 | 75 | 65 | 58 | 54 | 74 | 64 | 58 | 54 | 63 | 57 | 53 | 62 | 57 | 53 | 61 | 56 | 53 | 51 | | | | | | | | | | | | | | | | | | | |
| 9 | 71 | 61 | 54 | 50 | 70 | 60 | 54 | 50 | 59 | 53 | 50 | 58 | 53 | 49 | 57 | 53 | 49 | 48 | | | | | | | | | | | | | | | | | | | |
| 10 | 67 | 57 | 50 | 46 | 66 | 56 | 50 | 46 | 55 | 50 | 46 | 55 | 50 | 46 | 54 | 49 | 46 | 44 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° |
|-----|--------|
| 0° | 178204 |
| 5° | 177755 |
| 10° | 177370 |
| 15° | 177319 |
| 20° | 175584 |
| 25° | 164945 |
| 30° | 147044 |
| 35° | 117243 |
| 40° | 77847 |
| 45° | 46541 |
| 50° | 24120 |
| 55° | 12687 |
| 60° | 4480 |
| 65° | 78 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 46541 cd/sqm



TEST NUMBER: P786577

CATALOG NUMBER: LERS6D10D010-EC6DR700210IC9050-6LBS1H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 154.1 | 7.5 |
| 10°-20° | 442.0 | 21.4 |
| 20°-30° | 623.6 | 30.2 |
| 30°-40° | 538.3 | 26.1 |
| 40°-50° | 241.1 | 11.7 |
| 50°-60° | 63.1 | 3.1 |
| 60°-70° | 4.1 | 0.2 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1219.8 | 59.0 |
| 0°-40° | 1758.1 | 85.1 |
| 0°-60° | 2062.3 | 99.8 |
| 0°-90° | 2066.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2066.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1631 | |
| 5° | 1621 | 154 |
| 15° | 1568 | 442 |
| 25° | 1368 | 624 |
| 35° | 879 | 538 |
| 45° | 301 | 241 |
| 55° | 67 | 63 |
| 65° | 0 | 4 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P786577

CATALOG NUMBER: LERS6D10D010-EC6DR700210IC9050-6LBS1H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1631.0 |
| 2.5° | 1629.2 |
| 5° | 1620.7 |
| 7.5° | 1613.7 |
| 10° | 1598.7 |
| 12.5° | 1585.2 |
| 15° | 1567.6 |
| 17.5° | 1547.4 |
| 20° | 1510.1 |
| 22.5° | 1448.8 |
| 25° | 1368.2 |
| 27.5° | 1274.6 |
| 30° | 1165.5 |
| 32.5° | 1032.1 |
| 35° | 879.0 |
| 37.5° | 710.0 |
| 40° | 545.8 |
| 42.5° | 414.7 |
| 45° | 301.2 |
| 47.5° | 207.6 |
| 50° | 141.9 |
| 52.5° | 98.0 |
| 55° | 66.6 |
| 57.5° | 40.2 |
| 60° | 20.5 |
| 62.5° | 6.5 |
| 65° | 0.3 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)