

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788204

Luminaire Tested: LER6D08D010-EC6DR150210IC9035-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR150210IC9035-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 872.4 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct


Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P788204
CATALOG NUMBER: LER6D08D010-EC6DR150210IC9035-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P788204

CATALOG NUMBER: LER6D08D010-EC6DR150210IC9035-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1337615	1337615	1337615
5°	786039	775866	782004
10°	234594	236245	239856
15°	58350	59488	57656
20°	17461	20218	17829
25°	6154	7837	6232
30°	2261	2980	2299
35°	1133	1278	1097
40°	717	788	717
45°	525	567	525
50°	417	417	417
55°	348	348	348
60°	281	281	281
65°	214	214	214
70°	183	183	183
75°	113	113	151
80°	79	79	79
85°	42	42	42

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 567 cd/sqm



TEST NUMBER: P788204

CATALOG NUMBER: LER6D08D010-EC6DR150210IC9035-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	565.9	64.9
10°-20°	232.8	26.7
20°-30°	46.2	5.3
30°-40°	11.5	1.3
40°-50°	6.1	0.7
50°-60°	4.5	0.5
60°-70°	3.2	0.4
70°-80°	1.8	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	844.9	96.8
0°-40°	856.4	98.2
0°-60°	866.9	99.4
0°-90°	872.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	872.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	11888	11888	11888	11888	11888	
5°	7734	7655	7634	7687	7695	565
15°	672	684	685	673	664	230
25°	79	90	101	89	80	41
35°	16	17	18	17	15	11
45°	8	8	8	8	8	6
55°	5	5	5	5	5	4
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	0	0	0	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P788204

CATALOG NUMBER: LER6D08D010-EC6DR150210IC9035-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	11887.8	11887.8	11887.8	11887.8	11887.8
2.5°	10723.3	10732.3	10735.8	10746.4	10785.7
5°	7734.4	7654.9	7634.3	7687.1	7694.7
7.5°	4581.6	4597.7	4656.6	4669.7	4622.4
10°	2514.2	2534.9	2531.9	2550.0	2570.6
12.5°	1285.8	1269.7	1264.7	1285.3	1256.6
15°	671.8	684.4	684.9	672.8	663.8
17.5°	361.3	375.9	400.1	380.5	350.3
20°	213.4	226.5	247.1	231.0	217.9
22.5°	131.9	142.4	157.0	144.4	133.9
25°	79.0	89.6	100.6	89.1	80.0
27.5°	46.8	55.9	62.9	55.4	46.3
30°	30.2	35.2	39.8	34.7	30.7
32.5°	21.1	23.1	25.2	23.1	21.1
35°	15.6	16.6	17.6	16.6	15.1
37.5°	12.1	13.1	13.6	12.6	11.6
40°	10.1	10.6	11.1	10.6	10.1
42.5°	8.6	9.1	9.1	9.1	8.6
45°	7.5	7.5	8.1	7.5	7.5
47.5°	6.5	6.5	7.0	6.5	6.5
50°	6.0	6.0	6.0	6.0	6.0
52.5°	5.5	5.5	5.5	5.5	5.5
55°	5.0	5.0	5.0	5.0	5.0
57.5°	4.5	4.5	4.5	4.5	4.5
60°	4.0	4.0	4.0	4.0	4.0
62.5°	3.5	3.5	3.5	3.5	3.5
65°	3.0	3.0	3.0	3.0	3.0
67.5°	3.0	3.0	3.0	3.0	3.0
70°	2.5	2.5	2.5	2.5	2.5
72.5°	2.0	2.0	2.0	2.0	2.0
75°	1.5	1.5	1.5	1.5	2.0
77.5°	1.5	1.5	1.5	1.5	1.5
80°	1.0	1.0	1.0	1.0	1.0
82.5°	1.0	1.0	1.0	1.0	1.0
85°	0.5	0.5	0.5	0.5	0.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)