

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786615

Luminaire Tested: LERS6D15D010-EC6DR1515309035-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D15D010-EC6DR1515309035-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1471.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P786615
CATALOG NUMBER: LERS6D15D010-EC6DR1515309035-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P786615

CATALOG NUMBER: LERS6D15D010-EC6DR1515309035-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2255215	2255215	2255215
5°	1325271	1308116	1318462
10°	395531	398302	404395
15°	98383	100302	97201
20°	29440	34087	30062
25°	10376	13220	10509
30°	3811	5017	3879
35°	1910	2157	1852
40°	1207	1328	1207
45°	889	952	889
50°	709	709	709
55°	592	592	592
60°	477	477	477
65°	364	364	364
70°	307	307	307
75°	189	189	257
80°	134	134	134
85°	66	66	66

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 952 cd/sqm



TEST NUMBER: P786615

CATALOG NUMBER: LERS6D15D010-EC6DR1515309035-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	954.1	64.9
10°-20°	392.4	26.7
20°-30°	77.9	5.3
30°-40°	19.5	1.3
40°-50°	10.2	0.7
50°-60°	7.6	0.5
60°-70°	5.3	0.4
70°-80°	3.0	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1424.5	96.8
0°-40°	1443.9	98.2
0°-60°	1461.7	99.4
0°-90°	1471.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1471.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	20043	20043	20043	20043	20043	
5°	13040	12906	12872	12961	12973	952
15°	1133	1154	1155	1134	1119	388
25°	133	151	170	150	135	70
35°	26	28	30	28	26	18
45°	13	13	14	13	13	10
55°	8	8	8	8	8	8
65°	5	5	5	5	5	5
75°	2	2	2	2	3	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P786615

CATALOG NUMBER: LERS6D15D010-EC6DR1515309035-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	20042.8	20042.8	20042.8	20042.8	20042.8
2.5°	18079.4	18094.7	18100.7	18118.5	18184.7
5°	13040.3	12906.3	12871.5	12960.6	12973.3
7.5°	7724.6	7751.7	7851.0	7873.1	7793.3
10°	4239.0	4273.8	4268.7	4299.3	4334.0
12.5°	2167.9	2140.7	2132.2	2167.0	2118.7
15°	1132.7	1153.9	1154.8	1134.4	1119.1
17.5°	609.2	633.8	674.5	641.5	590.5
20°	359.8	381.8	416.6	389.5	367.4
22.5°	222.3	240.1	264.7	243.5	225.7
25°	133.2	151.0	169.7	150.2	134.9
27.5°	78.9	94.2	106.1	93.3	78.1
30°	50.9	59.4	67.0	58.5	51.8
32.5°	35.6	39.0	42.4	39.0	35.6
35°	26.3	28.0	29.7	28.0	25.5
37.5°	20.4	22.1	22.9	21.2	19.5
40°	17.0	17.8	18.7	17.8	17.0
42.5°	14.4	15.3	15.3	15.3	14.4
45°	12.7	12.7	13.6	12.7	12.7
47.5°	11.0	11.0	11.9	11.0	11.0
50°	10.2	10.2	10.2	10.2	10.2
52.5°	9.3	9.3	9.3	9.3	9.3
55°	8.5	8.5	8.5	8.5	8.5
57.5°	7.6	7.6	7.6	7.6	7.6
60°	6.8	6.8	6.8	6.8	6.8
62.5°	5.9	5.9	5.9	5.9	5.9
65°	5.1	5.1	5.1	5.1	5.1
67.5°	5.1	5.1	5.1	5.1	5.1
70°	4.2	4.2	4.2	4.2	4.2
72.5°	3.4	3.4	3.4	3.4	3.4
75°	2.5	2.5	2.5	2.5	3.4
77.5°	2.5	2.5	2.5	2.5	2.5
80°	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7
85°	0.8	0.8	0.8	0.8	0.8
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)