

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786622

Luminaire Tested: LERS6D15D010-EC6DR1515309050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D15D010-EC6DR1515309050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1493.9 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P786622
CATALOG NUMBER: LERS6D15D010-EC6DR1515309050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P786622

CATALOG NUMBER: LERS6D15D010-EC6DR1515309050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2290242	2290242	2290242
5°	1345861	1328432	1338940
10°	401680	404488	410684
15°	99911	101857	98713
20°	29890	34619	30528
25°	10540	13422	10672
30°	3871	5099	3939
35°	1939	2193	1874
40°	1221	1349	1221
45°	903	966	903
50°	716	716	716
55°	599	599	599
60°	484	484	484
65°	371	371	371
70°	314	314	314
75°	197	197	257
80°	134	134	134
85°	75	75	75

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 966 cd/sqm



TEST NUMBER: P786622

CATALOG NUMBER: LERS6D15D010-EC6DR1515309050-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	968.9	64.9
10°-20°	398.5	26.7
20°-30°	79.2	5.3
30°-40°	19.8	1.3
40°-50°	10.4	0.7
50°-60°	7.7	0.5
60°-70°	5.4	0.4
70°-80°	3.1	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1446.6	96.8
0°-40°	1466.3	98.2
0°-60°	1484.4	99.4
0°-90°	1493.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1493.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	20354	20354	20354	20354	20354	
5°	13243	13107	13071	13162	13175	967
15°	1150	1172	1173	1152	1136	394
25°	135	153	172	152	137	71
35°	27	28	30	28	26	18
45°	13	13	14	13	13	10
55°	9	9	9	9	9	8
65°	5	5	5	5	5	5
75°	3	3	3	3	3	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P786622

CATALOG NUMBER: LERS6D15D010-EC6DR1515309050-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	20354.1	20354.1	20354.1	20354.1	20354.1
2.5°	18360.2	18375.8	18381.8	18399.9	18467.1
5°	13242.9	13106.7	13071.4	13161.9	13174.8
7.5°	7844.6	7872.1	7972.9	7995.3	7914.3
10°	4304.9	4340.2	4335.0	4366.0	4401.4
12.5°	2201.5	2174.0	2165.4	2200.7	2151.6
15°	1150.3	1171.9	1172.7	1152.0	1136.5
17.5°	618.7	643.7	685.0	651.4	599.7
20°	365.3	387.7	423.1	395.5	373.1
22.5°	225.8	243.8	268.8	247.3	229.2
25°	135.3	153.4	172.3	152.5	137.0
27.5°	80.1	95.6	107.7	94.8	79.3
30°	51.7	60.3	68.1	59.5	52.6
32.5°	36.2	39.6	43.1	39.6	36.2
35°	26.7	28.4	30.2	28.4	25.8
37.5°	20.7	22.4	23.3	21.5	19.8
40°	17.2	18.1	19.0	18.1	17.2
42.5°	14.6	15.5	15.5	15.5	14.6
45°	12.9	12.9	13.8	12.9	12.9
47.5°	11.2	11.2	12.1	11.2	11.2
50°	10.3	10.3	10.3	10.3	10.3
52.5°	9.5	9.5	9.5	9.5	9.5
55°	8.6	8.6	8.6	8.6	8.6
57.5°	7.8	7.8	7.8	7.8	7.8
60°	6.9	6.9	6.9	6.9	6.9
62.5°	6.0	6.0	6.0	6.0	6.0
65°	5.2	5.2	5.2	5.2	5.2
67.5°	5.2	5.2	5.2	5.2	5.2
70°	4.3	4.3	4.3	4.3	4.3
72.5°	3.4	3.4	3.4	3.4	3.4
75°	2.6	2.6	2.6	2.6	3.4
77.5°	2.6	2.6	2.6	2.6	2.6
80°	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7
85°	0.9	0.9	0.9	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)