

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786637

Luminaire Tested: LERS6D15D010-EC6DR2015309030-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D15D010-EC6DR2015309030-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1480.0 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P786637
CATALOG NUMBER: LERS6D15D010-EC6DR2015309030-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P786637

CATALOG NUMBER: LERS6D15D010-EC6DR2015309030-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	95															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	98	96	95															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	98	96	95															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	98	96	95															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	98	96	95															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	98	96	95															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	98	96	95															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	98	96	95															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	920336
5°	830318
10°	466019
15°	236886
20°	100297
25°	46293
30°	24514
35°	13205
40°	7060
45°	4172
50°	2431
55°	1295
60°	830
65°	595
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4172 cd/sqm



TEST NUMBER: P786637

CATALOG NUMBER: LERS6D15D010-EC6DR2015309030-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	599.7	40.5
10°-20°	590.5	39.9
20°-30°	192.9	13.0
30°-40°	65.7	4.4
40°-50°	22.1	1.5
50°-60°	6.7	0.5
60°-70°	2.2	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1383.2	93.5
0°-40°	1448.9	97.9
0°-60°	1477.6	99.8
0°-90°	1480.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1480.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8423	
5°	7570	600
15°	2094	591
25°	384	193
35°	99	66
45°	27	22
55°	7	7
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786637

CATALOG NUMBER: LERS6D15D010-EC6DR2015309030-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8423.3
0.5°	8423.3
1°	8412.8
1.5°	8391.8
2°	8353.6
2.5°	8302.6
3°	8230.6
3.5°	8130.1
4°	7980.8
4.5°	7799.3
5°	7570.5
5.5°	7269.7
6°	6961.4
6.5°	6608.2
7°	6262.4
7.5°	5857.3
8°	5495.8
8.5°	5132.0
9°	4796.0
9.5°	4487.7
10°	4200.4
12.5°	3016.0
15°	2094.2
17.5°	1368.1
20°	862.6
22.5°	558.8
25°	384.0
27.5°	270.0
30°	194.3
32.5°	139.5
35°	99.0
37.5°	69.0
40°	49.5
42.5°	36.0
45°	27.0
47.5°	21.0
50°	14.3
52.5°	9.0
55°	6.8
57.5°	5.3
60°	3.8
62.5°	3.0
65°	2.3



TEST NUMBER: P786637
CATALOG NUMBER: LERS6D15D010-EC6DR2015309030-6LBS1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.5
70°		0.8

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)