

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786643

Luminaire Tested: LERS6D15D010-EC6DR2015309040-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P786643  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LERS6D15D010-EC6DR2015309040-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1774.5 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P786643  
CATALOG NUMBER: LERS6D15D010-EC6DR2015309040-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P786643

CATALOG NUMBER: LERS6D15D010-EC6DR2015309040-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94	94														
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	98	96	95	94	94														
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	95	93	92	91	91														
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	93	91	89	88	88														
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	91	88	86	85	85														
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	88	86	84	83	83														
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	86	84	82	81	81														
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	84	82	80	79	79														
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	82	80	78	77	77														
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	81	78	76	75	75														

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1103545
5°	995603
10°	558792
15°	284043
20°	120261
25°	55516
30°	29383
35°	15833
40°	8472
45°	5006
50°	2907
55°	1543
60°	983
65°	698
70°	288
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5006 cd/sqm



TEST NUMBER: P786643

CATALOG NUMBER: LERS6D15D010-EC6DR2015309040-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	719.1	40.5
10°-20°	708.1	39.9
20°-30°	231.3	13.0
30°-40°	78.8	4.4
40°-50°	26.5	1.5
50°-60°	8.0	0.4
60°-70°	2.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1658.5	93.5
0°-40°	1737.3	97.9
0°-60°	1771.8	99.8
0°-90°	1774.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1774.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10100	
5°	9078	719
15°	2511	708
25°	460	231
35°	119	79
45°	32	27
55°	8	8
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786643

CATALOG NUMBER: LERS6D15D010-EC6DR2015309040-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10100.1
0.5°	10100.1
1°	10087.5
1.5°	10062.3
2°	10016.5
2.5°	9955.3
3°	9869.0
3.5°	9748.4
4°	9569.5
4.5°	9351.8
5°	9077.5
5.5°	8716.8
6°	8347.2
6.5°	7923.6
7°	7509.0
7.5°	7023.3
8°	6589.8
8.5°	6153.6
9°	5750.7
9.5°	5381.0
10°	5036.6
12.5°	3616.4
15°	2511.1
17.5°	1640.5
20°	1034.3
22.5°	670.0
25°	460.5
27.5°	323.8
30°	232.9
32.5°	167.3
35°	118.7
37.5°	82.7
40°	59.4
42.5°	43.2
45°	32.4
47.5°	25.2
50°	17.1
52.5°	10.8
55°	8.1
57.5°	6.3
60°	4.5
62.5°	3.6
65°	2.7



TEST NUMBER: P786643  
CATALOG NUMBER: LERS6D15D010-EC6DR2015309040-6LBS1LI

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.8
70°		0.9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)