

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786710

Luminaire Tested: LERS6D15D010-EC6DR350215IC9040-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786710
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D15D010-EC6DR350215IC9040-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2473.5 lumens
Efficiency: N/A
Efficacy: 156.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786710

CATALOG NUMBER: LERS6D15D010-EC6DR350215IC9040-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P786710

CATALOG NUMBER: LERS6D15D010-EC6DR350215IC9040-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100														
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96					96														
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92					92														
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88					88														
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84					84														
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81					81														
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78					78														
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75					75														
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72					72														
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70					70														
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68					68														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	743629
5°	726157
10°	654461
15°	507966
20°	288113
25°	112093
30°	41811
35°	22915
40°	14976
45°	9117
50°	5796
55°	4096
60°	2994
65°	1629
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9117 cd/sqm



TEST NUMBER: P786710

CATALOG NUMBER: LERS6D15D010-EC6DR350215IC9040-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	608.9	24.6
10°-20°	1188.9	48.1
20°-30°	484.9	19.6
30°-40°	116.0	4.7
40°-50°	48.3	2.0
50°-60°	20.0	0.8
60°-70°	6.3	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2282.7	92.3
0°-40°	2398.7	97.0
0°-60°	2467.0	99.7
0°-90°	2473.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2473.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6806	
5°	6621	609
15°	4491	1189
25°	930	485
35°	172	116
45°	59	48
55°	22	20
65°	6	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786710

CATALOG NUMBER: LERS6D15D010-EC6DR350215IC9040-6LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	6806.0
2.5°	6765.2
5°	6620.8
7.5°	6332.8
10°	5898.9
12.5°	5288.0
15°	4490.7
17.5°	3515.7
20°	2477.9
22.5°	1580.0
25°	929.8
27.5°	525.6
30°	331.4
32.5°	232.7
35°	171.8
37.5°	132.9
40°	105.0
42.5°	80.9
45°	59.0
47.5°	44.2
50°	34.1
52.5°	27.1
55°	21.5
57.5°	17.4
60°	13.7
62.5°	10.0
65°	6.3
67.5°	2.2
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)