

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788608

Luminaire Tested: LER6D08D010-EC6DR600210IC9024-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788608  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D08D010-EC6DR600210IC9024-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1187.1 lumens  
Efficiency: N/A  
Efficacy: 133.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P788608

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9024-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P788608

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9024-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	154047
5°	157838
10°	159740
15°	152174
20°	134167
25°	108524
30°	73402
35°	36787
40°	5962
45°	5841
50°	5949
55°	6039
60°	6206
65°	6360
70°	6517
75°	6586
80°	6355
85°	5265

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 6586 cd/sqm



TEST NUMBER: P788608

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9024-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.5	11.6
10°-20°	372.1	31.3
20°-30°	400.4	33.7
30°-40°	174.0	14.7
40°-50°	29.2	2.5
50°-60°	28.4	2.4
60°-70°	24.3	2.0
70°-80°	16.3	1.4
80°-90°	4.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	910.0	76.7
0°-40°	1084.1	91.3
0°-60°	1141.7	96.2
0°-90°	1187.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1187.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1410	
5°	1439	138
15°	1345	372
25°	900	400
35°	276	174
45°	38	29
55°	32	28
65°	25	24
75°	16	16
85°	4	5
90°	0	



TEST NUMBER: P788608

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9024-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1409.9
2.5°	1449.5
5°	1439.1
7.5°	1442.4
10°	1439.8
12.5°	1410.1
15°	1345.3
17.5°	1258.3
20°	1153.9
22.5°	1042.2
25°	900.2
27.5°	720.0
30°	581.8
32.5°	448.4
35°	275.8
37.5°	118.0
40°	41.8
42.5°	38.5
45°	37.8
47.5°	36.5
50°	35.0
52.5°	33.4
55°	31.7
57.5°	30.1
60°	28.4
62.5°	26.6
65°	24.6
67.5°	22.6
70°	20.4
72.5°	18.0
75°	15.6
77.5°	12.8
80°	10.1
82.5°	7.2
85°	4.2
87.5°	1.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)