

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788633

Luminaire Tested: LER6D08D010-EC6DR600210IC9035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P788633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR600210IC9035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1508.3 lumens
Efficiency: N/A
Efficacy: 169.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788633

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P788633

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195719
5°	200535
10°	202954
15°	193348
20°	170468
25°	137880
30°	93260
35°	46737
40°	7588
45°	7417
50°	7564
55°	7677
60°	7889
65°	8066
70°	8274
75°	8359
80°	8054
85°	6770

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 8359 cd/sqm



TEST NUMBER: P788633

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	11.6
10°-20°	472.8	31.3
20°-30°	508.7	33.7
30°-40°	221.1	14.7
40°-50°	37.1	2.5
50°-60°	36.1	2.4
60°-70°	30.9	2.0
70°-80°	20.6	1.4
80°-90°	6.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1156.2	76.7
0°-40°	1377.4	91.3
0°-60°	1450.6	96.2
0°-90°	1508.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1508.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1791	
5°	1828	175
15°	1709	473
25°	1144	509
35°	350	221
45°	48	37
55°	40	36
65°	31	31
75°	20	21
85°	5	6
90°	0	



TEST NUMBER: P788633

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1791.3
2.5°	1841.7
5°	1828.4
7.5°	1832.6
10°	1829.3
12.5°	1791.6
15°	1709.3
17.5°	1598.8
20°	1466.1
22.5°	1324.1
25°	1143.7
27.5°	914.8
30°	739.2
32.5°	569.8
35°	350.4
37.5°	149.9
40°	53.2
42.5°	49.0
45°	48.0
47.5°	46.4
50°	44.5
52.5°	42.4
55°	40.3
57.5°	38.2
60°	36.1
62.5°	33.8
65°	31.2
67.5°	28.7
70°	25.9
72.5°	22.8
75°	19.8
77.5°	16.3
80°	12.8
82.5°	9.1
85°	5.4
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)