

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788641

Luminaire Tested: LER6D08D010-EC6DR600210IC9040-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P788641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR600210IC9040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1550.1 lumens
Efficiency: N/A
Efficacy: 174.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P788641
CATALOG NUMBER: LER6D08D010-EC6DR600210IC9040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P788641

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201138
5°	206085
10°	208568
15°	198687
20°	175188
25°	141689
30°	95846
35°	48031
40°	7788
45°	7633
50°	7785
55°	7886
60°	8107
65°	8299
70°	8498
75°	8612
80°	8306
85°	6895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 8612 cd/sqm



TEST NUMBER: P788641

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.6	11.6
10°-20°	485.9	31.3
20°-30°	522.8	33.7
30°-40°	227.2	14.7
40°-50°	38.2	2.5
50°-60°	37.1	2.4
60°-70°	31.7	2.0
70°-80°	21.3	1.4
80°-90°	6.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1188.2	76.7
0°-40°	1415.4	91.3
0°-60°	1490.7	96.2
0°-90°	1550.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1550.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1841	
5°	1879	180
15°	1756	486
25°	1175	523
35°	360	227
45°	49	38
55°	41	37
65°	32	32
75°	20	21
85°	6	6
90°	0	



TEST NUMBER: P788641

CATALOG NUMBER: LER6D08D010-EC6DR600210IC9040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1840.9
2.5°	1892.6
5°	1879.0
7.5°	1883.3
10°	1879.9
12.5°	1841.1
15°	1756.5
17.5°	1643.0
20°	1506.7
22.5°	1360.8
25°	1175.3
27.5°	940.1
30°	759.7
32.5°	585.5
35°	360.1
37.5°	154.0
40°	54.6
42.5°	50.3
45°	49.4
47.5°	47.7
50°	45.8
52.5°	43.6
55°	41.4
57.5°	39.3
60°	37.1
62.5°	34.7
65°	32.1
67.5°	29.5
70°	26.6
72.5°	23.5
75°	20.4
77.5°	16.8
80°	13.2
82.5°	9.3
85°	5.5
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)