

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788700

Luminaire Tested: LER6D08D010-EC6DR650210IC9050-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR650210IC9050-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1341.8 lumens
Efficiency: N/A
Efficacy: 150.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788700

CATALOG NUMBER: LER6D08D010-EC6DR650210IC9050-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P788700

CATALOG NUMBER: LER6D08D010-EC6DR650210IC9050-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71153
5°	70974
10°	70911
15°	68724
20°	62569
25°	54524
30°	45346
35°	35934
40°	25937
45°	16387
50°	8541
55°	4541
60°	2383
65°	1313
70°	546
75°	609
80°	437
85°	335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16387 cd/sqm



TEST NUMBER: P788700

CATALOG NUMBER: LER6D08D010-EC6DR650210IC9050-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.2	8.6
10°-20°	315.5	23.5
20°-30°	385.6	28.7
30°-40°	312.9	23.3
40°-50°	155.9	11.6
50°-60°	43.5	3.2
60°-70°	9.9	0.7
70°-80°	2.6	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	816.3	60.8
0°-40°	1129.2	84.2
0°-60°	1328.7	99.0
0°-90°	1341.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1341.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1218	
5°	1211	115
15°	1137	315
25°	846	386
35°	504	313
45°	198	156
55°	45	43
65°	10	10
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P788700

CATALOG NUMBER: LER6D08D010-EC6DR650210IC9050-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1218.3
2.5°	1217.4
5°	1210.6
7.5°	1206.6
10°	1195.7
12.5°	1173.5
15°	1136.6
17.5°	1079.0
20°	1006.7
22.5°	928.6
25°	846.1
27.5°	757.8
30°	672.4
32.5°	588.1
35°	504.0
37.5°	420.0
40°	340.2
42.5°	265.3
45°	198.4
47.5°	138.2
50°	94.0
52.5°	64.8
55°	44.6
57.5°	30.1
60°	20.4
62.5°	14.1
65°	9.5
67.5°	4.8
70°	3.2
72.5°	3.0
75°	2.7
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.5
87.5°	0.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)