

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788719

Luminaire Tested: LER6D08D010-EC6DR700210IC9030-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P788719
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR700210IC9030-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 796.9 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788719

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P788719

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97887
5°	94981
10°	92341
15°	91125
20°	85088
25°	63919
30°	45192
35°	16006
40°	8415
45°	8962
50°	9281
55°	9448
60°	9506
65°	9307
70°	8785
75°	8148
80°	7236
85°	5892

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 9517 cd/sqm



TEST NUMBER: P788719

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.7	10.3
10°-20°	224.1	28.1
20°-30°	246.8	31.0
30°-40°	94.3	11.8
40°-50°	44.5	5.6
50°-60°	44.2	5.6
60°-70°	35.4	4.4
70°-80°	20.4	2.6
80°-90°	5.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.5	69.3
0°-40°	646.8	81.2
0°-60°	735.5	92.3
0°-90°	796.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	896	
5°	866	82
15°	806	224
25°	530	247
35°	120	94
45°	58	45
55°	50	44
65°	36	35
75°	19	20
85°	5	6
90°	0	



TEST NUMBER: P788719

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	895.9
2.5°	886.6
5°	866.0
7.5°	848.9
10°	832.3
12.5°	818.2
15°	805.6
17.5°	775.1
20°	731.8
22.5°	638.5
25°	530.2
27.5°	461.6
30°	358.2
32.5°	231.4
35°	120.0
37.5°	64.8
40°	59.0
42.5°	58.6
45°	58.0
47.5°	56.7
50°	54.6
52.5°	52.2
55°	49.6
57.5°	46.8
60°	43.5
62.5°	39.9
65°	36.0
67.5°	31.8
70°	27.5
72.5°	23.3
75°	19.3
77.5°	15.2
80°	11.5
82.5°	8.1
85°	4.7
87.5°	1.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)