

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788720

Luminaire Tested: LER6D08D010-EC6DR700210IC9030-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788720  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D08D010-EC6DR700210IC9030-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1369.7 lumens  
Efficiency: N/A  
Efficacy: 153.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P788720  
CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P788720

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	168251
5°	163256
10°	158698
15°	156619
20°	146248
25°	109875
30°	77666
35°	27517
40°	14463
45°	15405
50°	15961
55°	16249
60°	16345
65°	16003
70°	15110
75°	14015
80°	12395
85°	10029

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 16370 cd/sqm



TEST NUMBER: P788720

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.4	10.3
10°-20°	385.1	28.1
20°-30°	424.1	31.0
30°-40°	162.1	11.8
40°-50°	76.5	5.6
50°-60°	76.1	5.6
60°-70°	60.9	4.4
70°-80°	35.0	2.6
80°-90°	9.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	949.6	69.3
0°-40°	1111.7	81.2
0°-60°	1264.3	92.3
0°-90°	1369.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1369.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1540	
5°	1488	140
15°	1385	385
25°	911	424
35°	206	162
45°	100	77
55°	85	76
65°	62	61
75°	33	35
85°	8	10
90°	0	



TEST NUMBER: P788720

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1539.9
2.5°	1523.8
5°	1488.5
7.5°	1459.0
10°	1430.4
12.5°	1406.3
15°	1384.6
17.5°	1332.2
20°	1257.8
22.5°	1097.4
25°	911.4
27.5°	793.4
30°	615.6
32.5°	397.7
35°	206.3
37.5°	111.4
40°	101.4
42.5°	100.7
45°	99.7
47.5°	97.5
50°	93.9
52.5°	89.7
55°	85.3
57.5°	80.5
60°	74.8
62.5°	68.5
65°	61.9
67.5°	54.6
70°	47.3
72.5°	40.0
75°	33.2
77.5°	26.1
80°	19.7
82.5°	13.9
85°	8.0
87.5°	3.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)