

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787116

Luminaire Tested: LER6D02D010-EC6DR300210IC9050-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P787116
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D02D010-EC6DR300210IC9050-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 697.1 lumens
Efficiency: N/A
Efficacy: 136.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P787116

CATALOG NUMBER: LER6D02D010-EC6DR300210IC9050-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P787116

CATALOG NUMBER: LER6D02D010-EC6DR300210IC9050-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	171580	171580	171580
5°	166657	166465	166664
10°	144349	143331	144318
15°	94181	93674	93206
20°	46829	48588	46772
25°	23589	26604	23107
30°	9448	10288	8229
35°	4382	4196	3513
40°	1888	2098	1779
45°	1331	1656	1342
50°	464	1203	488
55°	267	494	280
60°	184	214	184
65°	127	127	127
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 1656 cd/sqm



TEST NUMBER: P787116

CATALOG NUMBER: LER6D02D010-EC6DR300210IC9050-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.1	28.3
10°-20°	317.5	45.5
20°-30°	137.2	19.7
30°-40°	31.3	4.5
40°-50°	10.7	1.5
50°-60°	2.6	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	651.8	93.5
0°-40°	683.0	98.0
0°-60°	696.4	99.9
0°-90°	697.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	697.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2242	2242	2242	2242	2242	
5°	2169	2167	2166	2171	2169	197
15°	1188	1174	1182	1178	1176	318
25°	279	290	315	282	274	134
35°	47	48	45	45	38	32
45°	12	15	15	15	12	9
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P787116

CATALOG NUMBER: LER6D02D010-EC6DR300210IC9050-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2241.6	2241.6	2241.6	2241.6	2241.6
2.5°	2226.8	2225.2	2226.1	2227.2	2227.7
5°	2169.0	2166.9	2166.5	2171.0	2169.1
7.5°	2052.5	2049.5	2045.0	2055.2	2064.8
10°	1857.2	1853.9	1844.1	1849.0	1856.8
12.5°	1569.0	1558.3	1558.1	1573.5	1571.4
15°	1188.5	1174.2	1182.1	1178.3	1176.2
17.5°	799.2	793.7	804.3	801.1	787.3
20°	574.9	576.4	596.5	586.4	574.2
22.5°	419.5	424.7	448.6	422.5	412.9
25°	279.3	289.9	315.0	282.5	273.6
27.5°	171.8	176.6	202.1	169.6	164.8
30°	106.9	104.4	116.4	99.9	93.1
32.5°	70.1	67.0	70.9	63.6	58.1
35°	46.9	47.9	44.9	44.6	37.6
37.5°	29.3	33.7	29.7	31.7	24.2
40°	18.9	24.4	21.0	23.2	17.8
42.5°	15.5	18.8	17.3	18.4	15.8
45°	12.3	15.3	15.3	15.3	12.4
47.5°	6.8	10.2	13.1	10.5	7.3
50°	3.9	5.2	10.1	5.4	4.1
52.5°	2.6	3.0	6.9	3.1	2.8
55°	2.0	2.1	3.7	2.2	2.1
57.5°	1.5	1.7	2.0	1.7	1.5
60°	1.2	1.2	1.4	1.3	1.2
62.5°	0.9	0.9	1.0	0.9	0.9
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.3	0.4	0.4	0.4	0.4
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)