

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787135

Luminaire Tested: LER6D02D010-EC6DR350210IC9030-6LBDP1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P787135  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D02D010-EC6DR350210IC9030-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 523.0 lumens  
Efficiency: N/A  
Efficacy: 102.6 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P787135  
CATALOG NUMBER: LER6D02D010-EC6DR350210IC9030-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P787135

CATALOG NUMBER: LER6D02D010-EC6DR350210IC9030-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96											96																	
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92											92																	
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88											88																	
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84											84																	
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81											81																	
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78											78																	
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75											75																	
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72											72																	
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70											70																	
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68											68																	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	157237
5°	153538
10°	138383
15°	107403
20°	60915
25°	23701
30°	8844
35°	4842
40°	3166
45°	1931
50°	1224
55°	876
60°	634
65°	336
70°	32
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1931 cd/sqm



TEST NUMBER: P787135

CATALOG NUMBER: LER6D02D010-EC6DR350210IC9030-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.7	24.6
10°-20°	251.4	48.1
20°-30°	102.5	19.6
30°-40°	24.5	4.7
40°-50°	10.2	2.0
50°-60°	4.2	0.8
60°-70°	1.3	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	482.6	92.3
0°-40°	507.2	97.0
0°-60°	521.6	99.7
0°-90°	523.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	523.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1439	
5°	1400	129
15°	950	251
25°	197	103
35°	36	25
45°	12	10
55°	5	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P787135

CATALOG NUMBER: LER6D02D010-EC6DR350210IC9030-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1439.1
2.5°	1430.4
5°	1399.9
7.5°	1339.0
10°	1247.3
12.5°	1118.1
15°	949.5
17.5°	743.4
20°	523.9
22.5°	334.1
25°	196.6
27.5°	111.1
30°	70.1
32.5°	49.2
35°	36.3
37.5°	28.1
40°	22.2
42.5°	17.1
45°	12.5
47.5°	9.3
50°	7.2
52.5°	5.7
55°	4.6
57.5°	3.7
60°	2.9
62.5°	2.1
65°	1.3
67.5°	0.5
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)