

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787296

Luminaire Tested: LER6D02D010-EC6DR500210IC9040-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P787296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D02D010-EC6DR500210IC9040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 711.9 lumens
Efficiency: N/A
Efficacy: 139.6 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P787296

CATALOG NUMBER: LER6D02D010-EC6DR500210IC9040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P787296

CATALOG NUMBER: LER6D02D010-EC6DR500210IC9040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20								
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95																																				
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																																				
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85																																				
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80																																				
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76																																				
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72																																				
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69																																				
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65																																				
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62																																				
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125333
5°	124024
10°	121974
15°	111068
20°	92425
25°	65607
30°	34720
35°	14152
40°	5249
45°	2410
50°	986
55°	514
60°	262
65°	78
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2410 cd/sqm



TEST NUMBER: P787296

CATALOG NUMBER: LER6D02D010-EC6DR500210IC9040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.9	15.0
10°-20°	270.1	37.9
20°-30°	242.6	34.1
30°-40°	76.0	10.7
40°-50°	13.3	1.9
50°-60°	2.7	0.4
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.6	87.0
0°-40°	695.6	97.7
0°-60°	711.5	99.9
0°-90°	711.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	711.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1147	
5°	1131	107
15°	982	270
25°	544	243
35°	106	76
45°	16	13
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P787296

CATALOG NUMBER: LER6D02D010-EC6DR500210IC9040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1147.1
2.5°	1141.4
5°	1130.8
7.5°	1114.5
10°	1099.4
12.5°	1051.1
15°	981.9
17.5°	894.1
20°	794.9
22.5°	680.1
25°	544.2
27.5°	400.1
30°	275.2
32.5°	179.2
35°	106.1
37.5°	60.9
40°	36.8
42.5°	24.0
45°	15.6
47.5°	9.5
50°	5.8
52.5°	4.0
55°	2.7
57.5°	1.8
60°	1.2
62.5°	0.7
65°	0.3
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)