

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788903

Luminaire Tested: LER6D10D010-EC6DR250210IC9027-6LBDP1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788903  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D10D010-EC6DR250210IC9027-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1236.9 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P788903  
CATALOG NUMBER: LER6D10D010-EC6DR250210IC9027-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P788903

CATALOG NUMBER: LER6D10D010-EC6DR250210IC9027-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																												
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																												
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																												
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																												
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82																												
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																												
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77																												
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																												
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																												
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	512586
5°	477418
10°	340550
15°	200576
20°	124796
25°	68488
30°	31326
35°	11858
40°	5377
45°	3229
50°	1343
55°	857
60°	612
65°	414
70°	64
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3229 cd/sqm



TEST NUMBER: P788903

CATALOG NUMBER: LER6D10D010-EC6DR250210IC9027-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	374.1	30.2
10°-20°	506.7	41.0
20°-30°	268.1	21.7
30°-40°	66.2	5.4
40°-50°	16.2	1.3
50°-60°	4.2	0.3
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1148.9	92.9
0°-40°	1215.1	98.2
0°-60°	1235.5	99.9
0°-90°	1236.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1236.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4691	
5°	4353	374
15°	1773	507
25°	568	268
35°	89	66
45°	21	16
55°	4	4
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P788903

CATALOG NUMBER: LER6D10D010-EC6DR250210IC9027-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4691.4
2.5°	4614.3
5°	4352.9
7.5°	3827.5
10°	3069.5
12.5°	2320.4
15°	1773.2
17.5°	1381.9
20°	1073.3
22.5°	804.9
25°	568.1
27.5°	381.0
30°	248.3
32.5°	151.1
35°	88.9
37.5°	54.4
40°	37.7
42.5°	28.8
45°	20.9
47.5°	12.6
50°	7.9
52.5°	5.7
55°	4.5
57.5°	3.5
60°	2.8
62.5°	2.2
65°	1.6
67.5°	0.6
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)