

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787384

Luminaire Tested: LER6D02D010-EC6DR600210IC9035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P787384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D02D010-EC6DR600210IC9035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 669.7 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P787384
CATALOG NUMBER: LER6D02D010-EC6DR600210IC9035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P787384

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86906
5°	89037
10°	90122
15°	85843
20°	75694
25°	61218
30°	41407
35°	20754
40°	3366
45°	3291
50°	3366
55°	3410
60°	3496
65°	3594
70°	3674
75°	3715
80°	3586
85°	3009

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 3715 cd/sqm



TEST NUMBER: P787384

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.6	11.6
10°-20°	209.9	31.3
20°-30°	225.9	33.7
30°-40°	98.2	14.7
40°-50°	16.5	2.5
50°-60°	16.0	2.4
60°-70°	13.7	2.0
70°-80°	9.2	1.4
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.4	76.7
0°-40°	611.6	91.3
0°-60°	644.1	96.2
0°-90°	669.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	669.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	795	
5°	812	78
15°	759	210
25°	508	226
35°	156	98
45°	21	16
55°	18	16
65°	14	14
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P787384

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	795.4
2.5°	817.7
5°	811.8
7.5°	813.7
10°	812.3
12.5°	795.5
15°	758.9
17.5°	709.9
20°	651.0
22.5°	587.9
25°	507.8
27.5°	406.2
30°	328.2
32.5°	253.0
35°	155.6
37.5°	66.6
40°	23.6
42.5°	21.7
45°	21.3
47.5°	20.6
50°	19.8
52.5°	18.8
55°	17.9
57.5°	17.0
60°	16.0
62.5°	15.0
65°	13.9
67.5°	12.7
70°	11.5
72.5°	10.1
75°	8.8
77.5°	7.2
80°	5.7
82.5°	4.0
85°	2.4
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)