

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787393

Luminaire Tested: LER6D02D010-EC6DR600210IC9040-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P787393  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D02D010-EC6DR600210IC9040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 722.6 lumens  
Efficiency: N/A  
Efficacy: 141.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.84  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P787393  
CATALOG NUMBER: LER6D02D010-EC6DR600210IC9040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P787393

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93768
5°	96078
10°	97233
15°	92630
20°	81670
25°	66065
30°	44687
35°	22395
40°	3637
45°	3554
50°	3621
55°	3676
60°	3780
65°	3878
70°	3961
75°	4010
80°	3838
85°	3259

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 4010 cd/sqm



TEST NUMBER: P787393

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9040-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.7	11.6
10°-20°	226.5	31.3
20°-30°	243.7	33.7
30°-40°	105.9	14.7
40°-50°	17.8	2.5
50°-60°	17.3	2.4
60°-70°	14.8	2.0
70°-80°	9.9	1.4
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.0	76.7
0°-40°	659.9	91.3
0°-60°	695.0	96.2
0°-90°	722.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	722.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	858	
5°	876	84
15°	819	227
25°	548	244
35°	168	106
45°	23	18
55°	19	17
65°	15	15
75°	10	10
85°	3	3
90°	0	



TEST NUMBER: P787393

CATALOG NUMBER: LER6D02D010-EC6DR600210IC9040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	858.2
2.5°	882.4
5°	876.0
7.5°	878.0
10°	876.4
12.5°	858.4
15°	818.9
17.5°	766.0
20°	702.4
22.5°	634.4
25°	548.0
27.5°	438.3
30°	354.2
32.5°	273.0
35°	167.9
37.5°	71.8
40°	25.5
42.5°	23.5
45°	23.0
47.5°	22.2
50°	21.3
52.5°	20.3
55°	19.3
57.5°	18.3
60°	17.3
62.5°	16.2
65°	15.0
67.5°	13.7
70°	12.4
72.5°	10.9
75°	9.5
77.5°	7.8
80°	6.1
82.5°	4.4
85°	2.6
87.5°	0.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)