

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788960

Luminaire Tested: LER6D10D010-EC6DR300210IC9030-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR300210IC9030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1771.4 lumens
Efficiency: N/A
Efficacy: 151.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788960

CATALOG NUMBER: LER6D10D010-EC6DR300210IC9030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P788960

CATALOG NUMBER: LER6D10D010-EC6DR300210IC9030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	435991	435991	435991
5°	423473	422981	423496
10°	366796	364208	366711
15°	239316	238032	236835
20°	118999	123463	118844
25°	59947	67599	58714
30°	23996	26153	20912
35°	11129	10662	8933
40°	4806	5336	4526
45°	3388	4211	3421
50°	1167	3060	1227
55°	667	1268	707
60°	475	551	475
65°	308	308	308
70°	179	134	179
75°	0	89	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 4211 cd/sqm



TEST NUMBER: P788960

CATALOG NUMBER: LER6D10D010-EC6DR300210IC9030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	500.9	28.3
10°-20°	806.7	45.5
20°-30°	348.6	19.7
30°-40°	79.4	4.5
40°-50°	27.3	1.5
50°-60°	6.7	0.4
60°-70°	1.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1656.1	93.5
0°-40°	1735.6	98.0
0°-60°	1769.5	99.9
0°-90°	1771.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1771.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5696	5696	5696	5696	5696	
5°	5511	5506	5505	5516	5512	501
15°	3020	2984	3004	2994	2989	809
25°	710	737	800	718	695	340
35°	119	122	114	113	96	81
45°	31	39	39	39	32	22
55°	5	5	10	6	5	5
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P788960

CATALOG NUMBER: LER6D10D010-EC6DR300210IC9030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5696.0	5696.0	5696.0	5696.0	5696.0
2.5°	5658.3	5654.3	5656.6	5659.4	5660.5
5°	5511.4	5506.1	5505.0	5516.5	5511.7
7.5°	5215.3	5207.7	5196.3	5222.3	5246.6
10°	4719.2	4710.8	4685.9	4698.2	4718.1
12.5°	3986.8	3959.6	3959.1	3998.2	3992.9
15°	3020.0	2983.6	3003.8	2994.0	2988.7
17.5°	2030.9	2016.9	2043.7	2035.6	2000.7
20°	1460.9	1464.6	1515.7	1490.0	1459.0
22.5°	1066.0	1079.2	1139.9	1073.6	1049.3
25°	709.8	736.6	800.4	717.9	695.2
27.5°	436.5	448.8	513.4	430.9	418.6
30°	271.5	265.4	295.9	253.9	236.6
32.5°	178.1	170.3	180.1	161.6	147.7
35°	119.1	121.7	114.1	113.3	95.6
37.5°	74.4	85.6	75.5	80.5	61.5
40°	48.1	62.1	53.4	59.0	45.3
42.5°	39.4	47.8	43.9	46.7	40.3
45°	31.3	38.9	38.9	38.9	31.6
47.5°	17.3	26.0	33.3	26.6	18.5
50°	9.8	13.1	25.7	13.7	10.3
52.5°	6.7	7.6	17.6	7.8	7.0
55°	5.0	5.3	9.5	5.6	5.3
57.5°	3.9	4.2	5.0	4.2	3.9
60°	3.1	3.1	3.6	3.4	3.1
62.5°	2.2	2.2	2.5	2.2	2.2
65°	1.7	1.7	1.7	1.7	1.7
67.5°	0.8	1.1	1.1	1.1	1.1
70°	0.8	0.6	0.6	0.6	0.8
72.5°	0.6	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)