

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788983

Luminaire Tested: LER6D10D010-EC6DR300210IC9050-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR300210IC9050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1528.9 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788983

CATALOG NUMBER: LER6D10D010-EC6DR300210IC9050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P788983

CATALOG NUMBER: LER6D10D010-EC6DR300210IC9050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	376310	376310	376310
5°	365508	365085	365531
10°	316586	314356	316508
15°	206556	205447	204417
20°	102708	106569	102577
25°	51738	58342	50682
30°	20717	22573	18048
35°	9606	9204	7718
40°	4147	4606	3907
45°	2923	3637	2955
50°	1000	2644	1060
55°	574	1094	614
60°	413	475	413
65°	254	254	254
70°	157	112	157
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 3637 cd/sqm



TEST NUMBER: P788983

CATALOG NUMBER: LER6D10D010-EC6DR300210IC9050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	432.3	28.3
10°-20°	696.3	45.5
20°-30°	300.9	19.7
30°-40°	68.6	4.5
40°-50°	23.5	1.5
50°-60°	5.7	0.4
60°-70°	1.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1429.4	93.5
0°-40°	1498.0	98.0
0°-60°	1527.3	99.9
0°-90°	1528.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1528.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4916	4916	4916	4916	4916	
5°	4757	4752	4752	4761	4757	433
15°	2607	2575	2593	2584	2580	698
25°	613	636	691	620	600	293
35°	103	105	98	98	83	70
45°	27	34	34	34	27	19
55°	4	5	8	5	5	4
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P788983

CATALOG NUMBER: LER6D10D010-EC6DR300210IC9050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4916.3	4916.3	4916.3	4916.3	4916.3
2.5°	4883.7	4880.4	4882.3	4884.7	4885.7
5°	4757.0	4752.4	4751.5	4761.4	4757.3
7.5°	4501.4	4494.9	4485.0	4507.4	4528.4
10°	4073.2	4066.0	4044.5	4055.1	4072.2
12.5°	3441.0	3417.6	3417.2	3450.9	3446.4
15°	2606.6	2575.2	2592.6	2584.2	2579.6
17.5°	1752.9	1740.8	1764.0	1757.0	1726.8
20°	1260.9	1264.1	1308.3	1286.0	1259.3
22.5°	920.1	931.5	983.8	926.6	905.6
25°	612.6	635.8	690.8	619.6	600.1
27.5°	376.8	387.4	443.2	372.0	361.3
30°	234.4	229.1	255.4	219.2	204.2
32.5°	153.8	147.0	155.4	139.5	127.4
35°	102.8	105.0	98.5	97.8	82.6
37.5°	64.2	73.9	65.2	69.5	53.1
40°	41.5	53.6	46.1	50.9	39.1
42.5°	34.0	41.3	37.9	40.3	34.8
45°	27.0	33.6	33.6	33.6	27.3
47.5°	15.0	22.4	28.7	22.9	15.9
50°	8.4	11.3	22.2	11.8	8.9
52.5°	5.8	6.5	15.2	6.8	6.0
55°	4.3	4.6	8.2	4.8	4.6
57.5°	3.4	3.6	4.3	3.6	3.4
60°	2.7	2.7	3.1	2.9	2.7
62.5°	1.9	1.9	2.2	1.9	1.9
65°	1.4	1.4	1.4	1.4	1.4
67.5°	0.7	1.0	1.0	1.0	1.0
70°	0.7	0.5	0.5	0.5	0.7
72.5°	0.5	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)