

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787495

Luminaire Tested: LER6D02D010-EC6DR700210IC9050-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P787495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D02D010-EC6DR700210IC9050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 398.3 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P787495

CATALOG NUMBER: LER6D02D010-EC6DR700210IC9050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P787495

CATALOG NUMBER: LER6D02D010-EC6DR700210IC9050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48927
5°	47469
10°	46154
15°	45540
20°	42533
25°	31947
30°	22583
35°	8003
40°	4208
45°	4481
50°	4640
55°	4724
60°	4764
65°	4654
70°	4409
75°	4053
80°	3586
85°	2883

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 4764 cd/sqm



TEST NUMBER: P787495

CATALOG NUMBER: LER6D02D010-EC6DR700210IC9050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	10.3
10°-20°	112.0	28.1
20°-30°	123.3	31.0
30°-40°	47.1	11.8
40°-50°	22.3	5.6
50°-60°	22.1	5.6
60°-70°	17.7	4.4
70°-80°	10.2	2.6
80°-90°	2.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.1	69.3
0°-40°	323.3	81.2
0°-60°	367.7	92.3
0°-90°	398.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	398.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	448	
5°	433	41
15°	403	112
25°	265	123
35°	60	47
45°	29	22
55°	25	22
65°	18	18
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P787495

CATALOG NUMBER: LER6D02D010-EC6DR700210IC9050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	447.8
2.5°	443.1
5°	432.8
7.5°	424.3
10°	416.0
12.5°	409.0
15°	402.6
17.5°	387.4
20°	365.8
22.5°	319.1
25°	265.0
27.5°	230.7
30°	179.0
32.5°	115.6
35°	60.0
37.5°	32.4
40°	29.5
42.5°	29.3
45°	29.0
47.5°	28.4
50°	27.3
52.5°	26.1
55°	24.8
57.5°	23.4
60°	21.8
62.5°	19.9
65°	18.0
67.5°	15.9
70°	13.8
72.5°	11.6
75°	9.6
77.5°	7.6
80°	5.7
82.5°	4.0
85°	2.3
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)