

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789034

Luminaire Tested: LER6D10D010-EC6DR350210IC9050-6LBDP1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789034  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D10D010-EC6DR350210IC9050-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1742.0 lumens  
Efficiency: N/A  
Efficacy: 148.9 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P789034

CATALOG NUMBER: LER6D10D010-EC6DR350210IC9050-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P789034

CATALOG NUMBER: LER6D10D010-EC6DR350210IC9050-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																																				
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																																				
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																																				
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																																				
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																																				
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																																				
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																																				
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																																				
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																																				
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	523665
5°	511352
10°	460871
15°	357704
20°	202885
25°	78928
30°	29447
35°	16139
40°	10555
45°	6428
50°	4080
55°	2895
60°	2120
65°	1138
70°	96
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6428 cd/sqm



TEST NUMBER: P789034

CATALOG NUMBER: LER6D10D010-EC6DR350210IC9050-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	428.8	24.6
10°-20°	837.2	48.1
20°-30°	341.4	19.6
30°-40°	81.7	4.7
40°-50°	34.1	2.0
50°-60°	14.1	0.8
60°-70°	4.4	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1607.4	92.3
0°-40°	1689.2	97.0
0°-60°	1737.3	99.7
0°-90°	1742.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1742.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4793	
5°	4662	429
15°	3162	837
25°	655	341
35°	121	82
45°	42	34
55°	15	14
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P789034

CATALOG NUMBER: LER6D10D010-EC6DR350210IC9050-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4792.8
2.5°	4764.0
5°	4662.3
7.5°	4459.5
10°	4154.0
12.5°	3723.8
15°	3162.3
17.5°	2475.7
20°	1744.9
22.5°	1112.7
25°	654.7
27.5°	370.1
30°	233.4
32.5°	163.9
35°	121.0
37.5°	93.6
40°	74.0
42.5°	57.0
45°	41.6
47.5°	31.1
50°	24.0
52.5°	19.1
55°	15.2
57.5°	12.3
60°	9.7
62.5°	7.1
65°	4.4
67.5°	1.6
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)