

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787550

Luminaire Tested: LER6D05D010-EC6DR100210IC9050-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P787550  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D05D010-EC6DR100210IC9050-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 10° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 701.3 lumens  
Efficiency: N/A  
Efficacy: 93.5 lumens/watt  
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P787550  
CATALOG NUMBER: LER6D05D010-EC6DR100210IC9050-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P787550

CATALOG NUMBER: LER6D05D010-EC6DR100210IC9050-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |     |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|-----|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |    |    |    |     |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |    |    |    |     |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30 | 10 | 0   |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |     |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |    |    | 100 |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 116 | 114 | 113 | 111 | 114 | 112 | 111 | 109 | 108 | 107 | 106 | 104 | 104 | 103 | 101 | 101 | 100 | 98  |    |    |    |    |    | 98  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 105 | 104 | 102 | 103 | 101 | 100 | 99  | 98  | 98  | 97  |    |    |    |    |    | 97  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 111 | 107 | 104 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99  | 101 | 99  | 98  | 99  | 98  | 96  | 95  |    |    |    |    |    | 95  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 108 | 104 | 101 | 99  | 107 | 103 | 100 | 98  | 101 | 99  | 97  | 99  | 97  | 96  | 98  | 96  | 95  | 94  |    |    |    |    |    | 94  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 106 | 102 | 99  | 96  | 105 | 101 | 98  | 96  | 99  | 97  | 95  | 98  | 96  | 94  | 97  | 95  | 94  | 93  |    |    |    |    |    | 93  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 104 | 100 | 96  | 94  | 103 | 99  | 96  | 94  | 98  | 95  | 93  | 97  | 94  | 93  | 96  | 94  | 92  | 91  |    |    |    |    |    | 91  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 103 | 98  | 95  | 93  | 102 | 97  | 94  | 92  | 96  | 94  | 92  | 95  | 93  | 92  | 95  | 93  | 91  | 90  |    |    |    |    |    | 90  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 101 | 96  | 93  | 91  | 100 | 96  | 93  | 91  | 95  | 92  | 91  | 94  | 92  | 90  | 93  | 92  | 90  | 89  |    |    |    |    |    | 89  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 100 | 95  | 92  | 90  | 99  | 94  | 92  | 90  | 94  | 91  | 90  | 93  | 91  | 89  | 93  | 91  | 89  | 88  |    |    |    |    |    | 88  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 98  | 94  | 91  | 89  | 98  | 93  | 91  | 89  | 93  | 90  | 88  | 92  | 90  | 88  | 92  | 90  | 88  | 87  |    |    |    |    |    | 87  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1668390 |
| 5°  | 791152  |
| 10° | 162248  |
| 15° | 44545   |
| 20° | 17953   |
| 25° | 9620    |
| 30° | 5690    |
| 35° | 3708    |
| 40° | 2467    |
| 45° | 1607    |
| 50° | 884     |
| 55° | 667     |
| 60° | 371     |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1607 cd/sqm



TEST NUMBER: P787550

CATALOG NUMBER: LER6D05D010-EC6DR100210IC9050-6LBS1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 498.7  | 71.1      |
| 10°-20°   | 134.9  | 19.2      |
| 20°-30°   | 38.6   | 5.5       |
| 30°-40°   | 17.6   | 2.5       |
| 40°-50°   | 8.1    | 1.2       |
| 50°-60°   | 2.7    | 0.4       |
| 60°-70°   | 0.6    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 672.3  | 95.9      |
| 0°-40°    | 689.9  | 98.4      |
| 0°-60°    | 700.7  | 99.9      |
| 0°-90°    | 701.3  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 701.3  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 15270 |      |
| 5°  | 7213  | 499  |
| 15° | 394   | 135  |
| 25° | 80    | 39   |
| 35° | 28    | 18   |
| 45° | 10    | 8    |
| 55° | 4     | 3    |
| 65° | 0     | 1    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P787550

CATALOG NUMBER: LER6D05D010-EC6DR100210IC9050-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 15269.8 |
| 0.5°  | 15138.0 |
| 1°    | 14799.7 |
| 1.5°  | 14147.4 |
| 2°    | 13417.1 |
| 2.5°  | 12452.5 |
| 3°    | 11380.4 |
| 3.5°  | 10343.0 |
| 4°    | 9224.0  |
| 4.5°  | 8193.5  |
| 5°    | 7213.4  |
| 5.5°  | 6325.1  |
| 6°    | 5478.5  |
| 6.5°  | 4734.3  |
| 7°    | 4033.4  |
| 7.5°  | 3434.9  |
| 8°    | 2904.1  |
| 8.5°  | 2439.1  |
| 9°    | 2036.7  |
| 9.5°  | 1729.6  |
| 10°   | 1462.4  |
| 12.5° | 697.4   |
| 15°   | 393.8   |
| 17.5° | 239.4   |
| 20°   | 154.4   |
| 22.5° | 107.6   |
| 25°   | 79.8    |
| 27.5° | 59.0    |
| 30°   | 45.1    |
| 32.5° | 34.7    |
| 35°   | 27.8    |
| 37.5° | 20.8    |
| 40°   | 17.3    |
| 42.5° | 13.9    |
| 45°   | 10.4    |
| 47.5° | 6.9     |
| 50°   | 5.2     |
| 52.5° | 3.5     |
| 55°   | 3.5     |
| 57.5° | 1.7     |
| 60°   | 1.7     |
| 62.5° | 1.7     |
| 65°   | 0.0     |



TEST NUMBER: P787550  
CATALOG NUMBER: LER6D05D010-EC6DR100210IC9050-6LBS1MW

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



|       |  |     |
|-------|--|-----|
| 67.5° |  | 0.0 |
| 70°   |  | 0.0 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)