

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787573

Luminaire Tested: LER6D05D010-EC6DR150210IC9030-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P787573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D05D010-EC6DR150210IC9030-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 737.7 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P787573

CATALOG NUMBER: LER6D05D010-EC6DR150210IC9030-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P787573

CATALOG NUMBER: LER6D05D010-EC6DR150210IC9030-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1130859	1130859	1130859
5°	664541	655943	661127
10°	198335	199725	202785
15°	49335	50299	48744
20°	14761	17093	15072
25°	5204	6629	5266
30°	1909	2516	1947
35°	959	1082	930
40°	604	668	604
45°	448	476	448
50°	355	355	355
55°	299	299	299
60°	239	239	239
65°	186	186	186
70°	154	154	154
75°	98	98	128
80°	71	71	71
85°	33	33	33

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 476 cd/sqm



TEST NUMBER: P787573

CATALOG NUMBER: LER6D05D010-EC6DR150210IC9030-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	478.4	64.9
10°-20°	196.8	26.7
20°-30°	39.1	5.3
30°-40°	9.8	1.3
40°-50°	5.1	0.7
50°-60°	3.8	0.5
60°-70°	2.7	0.4
70°-80°	1.5	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.3	96.8
0°-40°	724.0	98.1
0°-60°	733.0	99.4
0°-90°	737.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	737.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	10050	10050	10050	10050	10050	
5°	6539	6472	6454	6499	6505	478
15°	568	579	579	569	561	195
25°	67	76	85	75	68	35
35°	13	14	15	14	13	9
45°	6	6	7	6	6	5
55°	4	4	4	4	4	4
65°	3	3	3	3	3	3
75°	1	1	1	1	2	2
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P787573

CATALOG NUMBER: LER6D05D010-EC6DR150210IC9030-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	10050.3	10050.3	10050.3	10050.3	10050.3
2.5°	9065.8	9073.4	9076.4	9085.3	9118.5
5°	6538.9	6471.7	6454.3	6498.9	6505.3
7.5°	3873.4	3887.0	3936.8	3947.9	3907.9
10°	2125.6	2143.1	2140.5	2155.8	2173.3
12.5°	1087.1	1073.4	1069.2	1086.6	1062.4
15°	568.0	578.6	579.1	568.8	561.2
17.5°	305.5	317.8	338.2	321.6	296.1
20°	180.4	191.5	208.9	195.3	184.2
22.5°	111.5	120.4	132.7	122.1	113.2
25°	66.8	75.7	85.1	75.3	67.6
27.5°	39.6	47.2	53.2	46.8	39.1
30°	25.5	29.8	33.6	29.4	26.0
32.5°	17.9	19.6	21.3	19.6	17.9
35°	13.2	14.0	14.9	14.0	12.8
37.5°	10.2	11.1	11.5	10.6	9.8
40°	8.5	8.9	9.4	8.9	8.5
42.5°	7.2	7.7	7.7	7.7	7.2
45°	6.4	6.4	6.8	6.4	6.4
47.5°	5.5	5.5	6.0	5.5	5.5
50°	5.1	5.1	5.1	5.1	5.1
52.5°	4.7	4.7	4.7	4.7	4.7
55°	4.3	4.3	4.3	4.3	4.3
57.5°	3.8	3.8	3.8	3.8	3.8
60°	3.4	3.4	3.4	3.4	3.4
62.5°	3.0	3.0	3.0	3.0	3.0
65°	2.6	2.6	2.6	2.6	2.6
67.5°	2.6	2.6	2.6	2.6	2.6
70°	2.1	2.1	2.1	2.1	2.1
72.5°	1.7	1.7	1.7	1.7	1.7
75°	1.3	1.3	1.3	1.3	1.7
77.5°	1.3	1.3	1.3	1.3	1.3
80°	0.9	0.9	0.9	0.9	0.9
82.5°	0.9	0.9	0.9	0.9	0.9
85°	0.4	0.4	0.4	0.4	0.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)